



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VPGL2HR 175W Heat-Resistant Globe

Appleton/Oz Gedney

Catalog Number	VPGL2HR
Manufacturer	Appleton/Oz Gedney
Description	Stylmaster Unilets Heat-Resistant Globe, Lamp Type: 200 - 300 WTT PS30 Medium Incandescent, Fixture Wattage: 200 - 300 WTT, Material: Prismatic Glass, Color: Clear, Finish: Natural, Enclosure: Nema 4X, Standard: Nec: Class I, Division 2,
Weight per unit	4.0 (lbs/each)
Product Category	Lighting Globes

Features

fixture wattage	200 - 300
Lamp Type	200 - 300 WTT PS30 Medium Incandescent
Material	PRISMATIC GLASS

Material, Color, and Finish

Color	Clear
-------	-------

Descriptions

Description	175W HEAT-RESISTANT GLOBE
extra long description	APP VPGL-2HR GLOBE PRISMATIC 300 WA
Long Description	Stylmaster UNILETS Heat-Resistant Globe, Lamp Type: 200 - 300 WTT PS30 Medium Incandescent, Fixture Wattage: 200 - 300 WTT, Material: Prismatic Glass, Color: Clear, Finish: Natural, Enclosure: NEMA 4X, Standard: NEC: Class I, Division 2,
Product Type	Globe Prismatic 300 Watt Max
Special Features	Modern styling with clean-line mounting hood and prismatic glass globe, plus optional guard; Prismatic globe, furnished as standard, eliminates glare and distributes light evenly; Globe seats firmly against composition gasket in mounting hood to keep out dirt and moisture; Full threads eliminate cross threading; Enclosed and gasketed lighting fixtures for use in storage areas, tunnels, subways, chemical plants and other areas where moisture, dirt or corrosive atmospheres are a problem; For use with threade

Manufacturer Information

Brand	Appleton
GTIN	00781381729154
Manufacturers Part Number	VPGL-2HR
UPC	781381729154



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Indoor HID Lighting
Type	Heat-Resistant Globe

Packaging

Carton	1
Weight Per each	4

Uses, Certifications, and Standards

Application	For Enclosed And Gasketed Lighting Fixtures
standard	NEC: Class I, Division 2, Groups A, B, C, D; CSA Certified: Class I, Division 2, Groups A, B, C, D, Class II, Division 1 And 2, Groups E, F, G, Class III, UL 1598, UL 844, UL E10444, C22.2 No. 250, C22.2 No. 137, CSA 025428