



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



VW150IM12 150W WL MNT V/T Fix

Lithonia Lighting - Acuity

Catalog Number	VW150IM12
Manufacturer	Lithonia Lighting - Acuity
Description	Utility Wall-Mounted Fixture For Entrances, Hallways, Closets, Tunnels, or Other Utility Applications
Weight per unit	2.5 (lbs/each)
Product Category	Incandescent Vapor Tight Light

Features

average life	Not Applicable
Ballast Type	Not Applicable
dimensions	Not Applicable
Hardware	Yes
Lamp Included	NO
Lamp Type	Incandescent
Material	Aluminum
Number of Lamps	1
pallet quantity	192
Power Source	Hardwired
Shape	Round
Socket Type	Medium: Screw
Voltage Rating	120
Warranty	2
Wattage	150

Material, Color, and Finish

Color	Gray
Finish	Gloss
fixture material	aluminum
Lens Material	Glass
Style	Traditional

Dimensions and Weight

Height	10.0000
Length	7.2500
Width	7.2500



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	150W WL MNT V/T FIX
extra long description	LITH VW150I M12 Utility vapor tight
Long Description	Utility wall-mounted fixture for entrances, hallways, closets, tunnels, or other utility applications
Product Type	Wallpack
Special Features	Utility wall-, ceiling- or pendant-mounted fixtures for entrances, hallways, closets, tunnels or other utility applications. Incandescent, fluorescent, metal halide or high pressure sodium sources are available.

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00745973817681
Manufacturers Part Number	VW150I M12
UPC	745973817681

Taxonomies, Classifications, and Categories

Type	Hazardous Industrial
------	----------------------

Packaging

Carton	1
Weight	2.0000
Weight Per each	2.5

Uses, Certifications, and Standards

Application	Education,Hospitality,Offices & Banks
environmental conditions	OUTDOOR
standard	cUL