



## WCBB Blu Twist-On Wire Conn

*Nsi Industries*

|                  |   |
|------------------|---|
| Catalog Number   | WCBB  |
| Manufacturer     | Nsi Industries  |
| Description      | The Easy-Twist WC-B-B 1,000-Count Bag Of Standard-Style Blue Wire Connectors Are Designed For Use On Copper Wires In The 22-14 Awg Size Range. They're Made Of Flame-Retardant Thermoplastic Rated For A Maximum Temperature Of 105°C (221°F). The Quick-Grip Square Spring Design Grips In Fewer Twists and Can Dead-End A Single Wire, While The Ergonomic Ribbed Texture Makes Them Easy to Twist. Their Compact Design Is Useful For Applications In Tight Areas or Anywhere Else You Need to Connect |
| Weight per unit  | 1.6 (lbs/each)  |
| Product Category | Electrical Fixture Conn ( Nuts  |

### Features

|                      |               |
|----------------------|---------------|
| Material             | Thermoplastic |
| Number of Conductors | 1             |
| Voltage Rating       | 300           |
| Warranty             | 1 YEAR        |
| Wire Type            | CU Wire Only  |

### Material, Color, and Finish

|        |               |
|--------|---------------|
| Color  | Blue          |
| Finish | Thermoplastic |

### Dimensions and Weight

|      |                           |
|------|---------------------------|
| Size | H=.697 - W=.390 - ID=.161 |
|------|---------------------------|



## Descriptions

|                        |   |
|------------------------|---|
| Description            | BLU TWIST-ON WIRE CONN  |
| extra long description | NSI WC-B-B Easy-Twist Blue - 1000 B   |
| Features               | Connecting wires is faster and easier than ever with the professional performance features of Easy-Twist wire connectors from NSI. These connectors feature a specialized design to install in half the time of a typical wire connector, saving you time and energy. The conical screw shape grips in fewer twists and the outside of the connector is textured with easy-grip ribs for comfortable twisting. The expert team at NSI designed these connectors with key convenience and performance features for electrical in |
| Long Description       | The Easy-Twist WC-B-B 1,000-Count Bag of Standard-Style Blue Wire Connectors are designed for use on copper wires in the 22-14 AWG size range. They're made of flame-retardant thermoplastic rated for a maximum temperature of 105°C Celsius (221°F Fahrenheit). The quick-grip square spring design grips in fewer twists and can dead-end a single wire, while the ergonomic ribbed texture makes them easy to twist. Their compact design is useful for applications in tight areas or anywhere else you need to connect    |
| Product Type           | Easy-Twist Blue - 1000 Bag  |
| Special Features       | Standard Blue Wire Connector - 1,000 Pcs Bag  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSI            |
| GTIN                      | 00662381140128 |
| Manufacturers Part Number | WC-B-B         |
| UPC                       | 662381140128   |

## Taxonomies, Classifications, and Categories

|                      |                          |
|----------------------|--------------------------|
| Category Description | WIRE NUTS                |
| Type                 | Standard Wire Connectors |

## Availability

|             |      |
|-------------|------|
| minimum qty | 1000 |
|-------------|------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 1000 |
| Weight Per each | 1.61 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100  
78217-0000, TX San Antonio  
Phone: 210-646-6950  
Fax: 210-646-6192

## Uses, Certifications, and Standards

|                          |               |
|--------------------------|---------------|
| Application              | Splicing Wire |
| environmental conditions | 105 C         |
| standard                 | UL 486C       |
| Temperature Rating       | 105 C         |