



## WF6LED30K40K50KM \*Delisted\* 6" 14W Led Wafer 3K/4K/5K WHT 120-277V

*Lithonia Lighting - Acuity*

Catalog Number	WF6LED30K40K50KM
Manufacturer	Lithonia Lighting - Acuity
Description	Lith WF6 Led 30K40K50K MVolt 90cri
Weight per unit	1.7 (lbs/each)
Product Category	Lighting

### Features

dimmable	Yes
Lamp Included	Yes
Lamp Type	LED - Dynamic
lumens	1100 LM
Material	Aluminum
Maximum Operating Temperature	25
pallet quantity	450
Power Source	Hardwired
Shape	Round
Voltage Rating	120-277
Warranty	5
Wattage	14

### Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	Variable
Finish	Matte
Lens Color	WHITE
Lens Material	Polycarbonate

### Dimensions and Weight

Height	1.14
Length	6.7
Width	6.7

### Descriptions

Construction	Canless, New Construction, Remodel
Description	*DELISTED* 6" 14W LED WAFER 3K/4K/5K WHT 120-277V
Long Description	LITH WF6 LED 30K40K50K MVOLT 90CRI
Product Type	Downlight



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

106 Industrial Drive  
71292-0000, LA West Monroe  
Phone: 318-398-9757  
Fax: 318-398-9704

## Manufacturer Information

Brand	Lithonia Lighting
GTIN	00193047884716
Manufacturers Part Number	WF6 LED 30K40K50K MVOLT 90CRI
UPC	193047884716

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Downlight

## Trade Size

aperture size	6 in
---------------	------

## Availability

Manufacturer Status	Inactive
---------------------	----------

## Packaging

Carton	1
Package	6
Weight	1.6
Weight Per each	1.7

## Uses, Certifications, and Standards

Application	Education, Hospitality, House of Worship, Residential, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSACA Title 24, JA8