



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## WP3425IV RJ25 Conn Iv (M20)

Pass & Seymour/Legrand

Catalog Number	WP3425IV
Manufacturer	Pass & Seymour/Legrand
Description	This High-Quality RJ25 (6P6C) Keystone Connector Is Designed For Use In Any Keystone Wall Plate. It Features Rear Retention Caps to Ensure Secure Wire Termination, Making It A Reliable Choice For Your Network Setup.
Weight per unit	0.0321 (lbs/each)
Product Category	Outlets, Jacks, & Plates

### Features

connection	RJ25 Female
insulation	Insulation Resistance: > 10
Resistance	500 (@ 100 VDC)

### Material, Color, and Finish

Color	Ivory
Finish	Smooth plastic

### Dimensions and Weight

Size	1.1 x 0.67 x 0.87 (27.95 x 16.90 x 22)
------	--

### Descriptions

Description	RJ25 CONN IV (M20)
extra long description	OnQ WP3425IV RJ25 CONNECTOR IVORY (
Features	This high-quality RJ25 (6P6C) Keystone Connector is designed for use in any Keystone wall plate. It features rear retention caps to ensure secure wire termination, making it a reliable choice for your network setup.
Long Description	This high-quality RJ25 (6P6C) Keystone Connector is designed for use in any Keystone wall plate. It features rear retention caps to ensure secure wire termination, making it a reliable choice for your network setup.
Product Type	RJ25 Connector Ivory (M20)
Special Features	Quick Connect

### Manufacturer Information

Brand	Legrand On-Q
GTIN	00804428024996
Manufacturers Part Number	WP3425-IV
UPC	804428024996



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	RJ25 6-Position, 6-Conductor Telephone connector

## Packaging

Carton	20
Package	120
Weight Per each	0.0321

## Uses, Certifications, and Standards

Application	Residential
Enclosure	High Impact Flame Retardant Plastic
environmental conditions	10 to 93 (relative humidity, non-condensing)
Mounting standard	Keystone opening CSA, cULus, RoHS
Temperature Rating	-10 to 60 F (-23.33 to 15.56 C)