



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



WP3475IV Cat 5E QC A/B Keystone Conn Iv (M10)

Pass & Seymour/Legrand

Catalog Number	WP3475IV
Manufacturer	Pass & Seymour/Legrand
Description	Keystone Insert, Structured Wiring Application, Ivory Color, 1 CT;10 PK Package Quantity, Easily Terminate All Four Pairs Using The Legrand Punch & Go Tool (AC3400);RJ45 Inserts Can Be Terminated With Any 110 Punchdown Tool Special Features, Eia/Tia 568A/B Standards Met, 0.04 LB Weight
Weight per unit	0.0417 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

connection	RJ45 Female
insulation	Electrical Insulation Resistance: 500 (@ 100 VDC)

Material, Color, and Finish

Finish	Smooth plastic
--------	----------------

Dimensions and Weight

Size	0.76 x 0.67 x 1.18 (19.30 x 16.9 x 30)
------	----------------------------------------

Descriptions

Description	CAT 5E QC A/B KEYSTONE CONN IV (M10)
extra long description	OnQ WP3475IV CAT 5E QC A/B KEYSTONE

Manufacturer Information

Brand	LEGRAND-ON-Q
GTIN	00804428036678
Manufacturers Part Number	WP3475-IV
UPC	804428036678

Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	RJ45 Female Cat 5e Keystone Insert

Packaging

Carton	10
Package	60
Weight Per each	0.0417



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	Housing Material: High Impact Flame Retardant Plastic
environmental conditions	0 to 93 (relative humidity, non-condensing)
Mounting	Keystone opening
standard	CSA, cULus, RoHS, ANSI/UL 1863, Flame-Retardant Plastic UL 94V-0
Temperature Rating	14 to 140 F (-10 to 60 C)