



Pass and Seymour
Weatherproof Two Gang Box, Gray
Part No. WPB282



Weatherproof 2 Gang Box, 7 hole 1/2, 30.5 Cu.In., Gray (2 Holes Each End, 1 Hole Each side, 1 Hole in Back)

Features & Benefits

Wide range of sizes, depths, and gangs.

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

2 closure plugs and mounting lugs furnished with all boxes.

UL Listed for wet and/or damp locations with appropriate cover.

Designed for both interior and exterior applications.

Will accept standard 4 screw mounting covers and single gang weatherproof covers.

Simply strike desired knockout studs with a sharp hammer blow for clean mounting holes.

Heavy die-cast aluminum.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007116472	Country Of Origin	India
Material	Die-Cast Aluminum	Features	Corrosion Resistant, Weatherproof
Number of Knockouts	7	Application Sector	Commercial, Residential
Standard	UL Listed	Warranty Type	1-Year Limited Warranty
Type	Weatherproof		

Dimensions

Product Width US	4.5 in	Product Weight US	1.06 lb
------------------	--------	-------------------	---------

Product Volume US	30.5 cu in	Product Depth US	2.24 in
Product Height US	4.5 in	Product Length US	4.5 in
Cubic Capacity	30.5 in ³	Box Depth	Shallow

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	143223
------------	-----	-----------------	--------

Technical Information

Number of Gangs	1	Size of Threaded Openings	1/2 in
Indoor/Outdoor	Both	Cable Entry	Back, Bottom, Side, Top
Box Shape	Square	Mounting Type	Screw Mount