



Pass and Seymour
Weatherproof Two Gang Deep Box, Gray
Part No. WPBD252



Weatherproof 2 Gang Deep Box, 5 Hole 1/2, 37 Cu.In. with Threaded Holes, Gray (2 Holes Each End, 1 Hole in Back)

Features & Benefits

Baked-on electrostatic, polyester, powder paint for superior scratch and corrosion resistance.

4 closure plugs and mounting lugs furnished with all boxes.

UL listed for wet and/or damp locations with appropriate cover. Designed for both interior and exterior applications.

Will accept standard three-gang weatherproof covers.

Simply strike desired knockout studs with a sharp hammer blow for clean mounting holes.

Heavy die-cast aluminum.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007116045	Country Of Origin	India
Material	Die-Cast Aluminum	Features	Corrosion Resistant, Deep, Weatherproof
Number of Knockouts	5	Application Sector	Commercial, Residential
Standard	UL Listed	Warranty Type	1-Year Limited Warranty
Type	Weatherproof		

Dimensions

Product Width US	4.5 in	Product Depth US	2.72 in
Product Height US	4.5 in	Cubic Capacity	37 in ³

Box Depth	Deep		
Technical Information			
Number of Gangs	2	Size of Threaded Openings	1/2 in
Indoor/Outdoor	Both	Cable Entry	Back, Bottom, Top
Box Shape	Square	Mounting Type	Screw Mount