



WW-716

GENERAL Vinyl Electrical Tape

COLOR

- Black

SPECIFICATIONS

Thickness	7 mil
Adhesion to steel	16 oz/in
Adhesion to backing	16 oz/in
Tensile strength	15 lb/in
Elongation	200%
Operating temperature	20°F - 176°F
Dielectric strength	1200 V/mil
Certification	UL/CSA

APPLICATIONS

- Used as primary insulation for wire and cable splices up to 600 volts
- Used for wire harnessing
- Used for jacketing on high voltage splices

KEY FEATURES

- Good adhesion and elasticity
- All weather performance
- Great tensile strength
- Resistant to UV, abrasion and corrosion
- Flame-retardant

DIMENSIONS

- Thickness: .007"
- Width: ¾"
- Length: 60'

COMPOSITION

- Backing: Plasticized polyvinylchloride (PVC)
- Adhesive material: rubber-based

APPLICABLE REGULATORY STANDARDS

- UL Listed; UL Standard 510
- CSA Certified; CSA Standard C22.2

STORAGE CONDITIONS

Product should be stored in humidity-controlled, dry conditions between 50°F and 73°F (10°C and 23°C). Relative humidity should be less than 65%.





WW-716

GENERAL Vinyl Electrical Tape

COLOR

- Black

SPECIFICATIONS

Thickness	7 mil
Adhesion to steel	16 oz/in
Adhesion to backing	16 oz/in
Tensile strength	15 lb/in
Elongation	200%
Operating temperature	20°F - 176°F
Dielectric strength	1200 V/mil
Certification	UL/CSA

APPLICATIONS

- Used as primary insulation for wire and cable splices up to 600 volts
- Used for wire harnessing
- Used for jacketing on high voltage splices

KEY FEATURES

- Good adhesion and elasticity
- All weather performance
- Great tensile strength
- Resistant to UV, abrasion and corrosion
- Flame-retardant

DIMENSIONS

- Thickness: .007"
- Width: ¾"
- Length: 60'

COMPOSITION

- Backing: Plasticized polyvinylchloride (PVC)
- Adhesive material: rubber-based

APPLICABLE REGULATORY STANDARDS

- UL Listed; UL Standard 510
- CSA Certified; CSA Standard C22.2

STORAGE CONDITIONS

Product should be stored in humidity-controlled, dry conditions between 50°F and 73°F (10°C and 23°C). Relative humidity should be less than 65%.

