



Powering Business Worldwide

pe.eaton.com

IDC-Multi-Conductor Terminal Blocks

XBQT15D22

UPC:782116926862

Dimensions:

- **Height:** X
- **Length:** 3.7 IN
- **Width:** .2 IN

Warranties:

- 1 year

Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** 15A (EN), 10A (UL), 17.50A connection
- **Voltage Rating:** EN 550V, UL 600V, 800V connection
- **Maximum Wire Size:** 16 AWG/1.5 mm²
- **Quantity:** 50
- **Wire Size:** #24-16 AWG
- **Color:** Gray
- **Number Of Wires:** Four-wire

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBQT15D22](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

IDC-Multi-Conductor Terminal Blocks

XBQT15D22

UPC:782116926862

Dimensions:

- **Height:** X
- **Length:** 3.7 IN
- **Width:** .2 IN

Warranties:

- 1 year

Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** 15A (EN), 10A (UL), 17.50A connection
- **Voltage Rating:** EN 550V, UL 600V, 800V connection
- **Maximum Wire Size:** 16 AWG/1.5 mm²
- **Quantity:** 50
- **Wire Size:** #24-16 AWG
- **Color:** Gray
- **Number Of Wires:** Four-wire

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBQT15D22](#)

Certifications:

- CSA Certified
- UL Listed

Product compliance: No Data



