

Eaton XBUT35

Catalog Number: XBUT35

Eaton XB IEC terminal block, 16 mm Screw connection single level-through-feed, Gray, 8 AWG/6 mm² maximum wire, IEC 800V, EN 700V, UL 600V, IEC #24-8 AWG, EN #24-8 AWG, UL #24-8 AWG wire, IEC 57A, EN 40,50A, UL 50A



General specifications

Product Name	Catalog Number
Eaton XB IEC terminal block	XBUT35
UPC	Product Length/Depth
782116905065	2.37 in
Product Height	Product Width
2.88 in	0.63 in
Product Weight	Warranty
0.02 lb	1 year
Certifications	
CSA Certified	
UL Listed	

Product specifications

Type

IEC-XB Series

Amperage Rating

527 (IEC), 40A (EN), 50A (EN), 50A (UL)

Voltage rating

IEC 800V, EN 700V, UL 600V

Resources

Brochures

[XB IEC TERMINAL BLOCKS](#)

[XB IEC terminal blocks—versatility, quality, and reliability](#)

Drawings

[XBUT35 2D PDF](#)

[XBUT35 2D Drawing Xchange](#)

[XBUT35 3D Inventor](#)

[XBUT35 AutoCAD 2D Footprint](#)

[XBUT35 AutoCAD 2D Footprint \(mm\)](#)

[XBUT35 3D Model Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - XBUT35](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)