

Specifications

Eaton XJG54 HDG



Photo is representative

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 4" maximum conduit movement, 1-1/2" trade size

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series XJG expansion coupling
CATALOG NUMBER	XJG54 HDG
UPC	662276271494
PRODUCT LENGTH/DEPTH	8 in
PRODUCT HEIGHT	3.62 in
PRODUCT WIDTH	3.62 in
PRODUCT WEIGHT	6.2 lb

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC

Product specifications

TYPE	Expansion
CONDUIT TYPE	Rigid/IMC
TRADE SIZE	1-1/2"
CONDUIT MOVEMENT - MAX	4"
MATERIAL	Steel
FINISH	Hot dip galvanized

Resources

BROCHURES	Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure
	Crouse-Hinds series Hot Dip Galvanized Products brochure
CATALOGS	Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page
CERTIFICATION REPORTS	XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification
INSTALLATION INSTRUCTIONS	IF 1508 - Assembly-Free XJG IF 343 - Type XJ Expansion Joints
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XJG54 HDG Expansion and Deflection Couplings

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.