

# Eaton XJG64 HDG

Catalog Number: XJG64 HDG

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 4" maximum conduit movement, 2" trade size

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series XJG expansion coupling	XJG64 HDG
	UPC
	662276271517
<b>Product Length/Depth</b>	<b>Product Height</b>
8.75 in	4.38 in
<b>Product Width</b>	<b>Product Weight</b>
4.38 in	8.9 lb

Photo is representative

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

## Product specifications

### Type

Expansion

### Conduit type

Rigid/IMC

### Trade size

2"

### Conduit movement - max

4"

### Material

Steel

### Finish

Hot dip galvanized

## Resources

### Brochures

[Crouse-Hinds series Hot Dip Galvanized Products brochure](#)

[Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

### Catalogs

[Crouse-Hinds series XJG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

### Certification reports

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

[XJG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

### Installation instructions

[IF 343 - Type XJ Expansion Joints](#)

[IF 1508 - Assembly-Free XJG](#)

### Specifications and datasheets

[Expansion and Deflection Couplings](#)

[Eaton Specification Sheet - XJG64 HDG](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)