

# Specifications



## Eaton XTCE065DS1A

Eaton XT IEC contactor, 65A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/20, 25, 50, 60 hp(1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCE065DS1A
<b>UPC</b>	786685365121
<b>PRODUCT LENGTH/DEPTH</b>	1 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	CSA Certified UL Listed EN 60947 IEC 60947



Powering Business Worldwide

## Product specifications

AMPERAGE RATING	65A
HP RATING - MAX	5, 10, 15/ 20, 25, 50, 60 hp (1/3PH @ 115,200,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage non-reversing contactor
FREQUENCY RATING	50-60 Hz
FRAME SIZE	55 mm
TERMINALS	Screw terminals
COIL	110-120 Vac, 50/60 Hz
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	65 A
SERIES	XT IEC
OPERATION	Non-reversing

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - XTCE065DS1A</a>
WARRANTY GUIDES	<a href="#">Selling Policy 25-000 - Distribution and Control Products and Services</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest  
product and support information.

All other trademarks are property of  
their respective owners.



# Specifications



Photo is representative



## Eaton XTCE065DS1A

Eaton XT IEC contactor, 65A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/20, 25, 50, 60 hp(1/3PH @ 115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

### General specifications

<b>PRODUCT NAME</b>	Eaton XT IEC contactor
<b>CATALOG NUMBER</b>	XTCE065DS1A
<b>UPC</b>	786685365121
<b>PRODUCT LENGTH/DEPTH</b>	1 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	1 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	CSA Certified UL Listed EN 60947 IEC 60947



Powering Business Worldwide

## Product specifications

AMPERAGE RATING	65A
HP RATING - MAX	5, 10, 15/ 20, 25, 50, 60 hp (1/3PH @ 115,200,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage non-reversing contactor
FREQUENCY RATING	50-60 Hz
FRAME SIZE	55 mm
TERMINALS	Screw terminals
COIL	110-120 Vac, 50/60 Hz
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	65 A
SERIES	XT IEC
OPERATION	Non-reversing

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - XTCE065DS1A</a>
WARRANTY GUIDES	<a href="#">Selling Policy 25-000 - Distribution and Control Products and Services</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest  
product and support information.

All other trademarks are property of  
their respective owners.

