

Specifications

Photo is representative

Eaton XTCE065DS1A

Eaton XT IEC contactor, 65A, Side-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 65A, Frame D, 55 mm, 50-60 Hz, 5, 10, 15/20, 25, 50, 60 hp(1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR

General specifications

PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCE065DS1A
UPC	786685365121
PRODUCT LENGTH/DEPTH	1 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	1 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	CSA Certified UL Listed EN 60947 IEC 60947

Product specifications

AMPERAGE RATING	65A
HP RATING - MAX	5, 10, 15/ 20, 25, 50, 60 hp (1/3PH @115,200,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
TYPE	Full voltage non-reversing contactor
FREQUENCY RATING	50-60 Hz
FRAME SIZE	55 mm
TERMINALS	Screw terminals
COIL	110-120 Vac, 50/60 Hz
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	65 A
SERIES	XT IEC
OPERATION	Non-reversing

Resources

CATALOGS	Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - XTCE065DS1A
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

