

# Eaton XTCR025C21A

Catalog Number: XTCR025C21A

Eaton XT IEC contactor, 25A, 110 Vac 50 Hz, 120 Vac 60 Hz, 2NO-2NO, 25A, Frame C, 45 mm, 50-60 Hz, 2, 5/ 7.5, 10, 15, 20 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, , Screw terminals, FVR

## General specifications



**Product Name**  
Eaton XT IEC contactor

**Catalog Number**  
XTCR025C21A

**UPC**  
786685180236

**Product Length/Depth**  
7.5 in

**Product Height**  
4.5 in

**Product Width**  
4.75 in

**Product Weight**  
2.45 lb

**Certifications**  
UL Listed

## Product specifications

### Amperage Rating

25A

### HP rating - max

2, 5/ 7.5, 10, 15, 20 hp (1/3PH @115,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage reversing contactor

### Frequency rating

50-60 Hz

### Terminals

Screw terminals

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

2 NO, 2 NO

### Continuous ampere rating

25 A

### Series

XT IEC

### Operation

Reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCR\\_C 3D Model Xchange](#)

[XTCR\\_C 2D Drawing Xchange](#)

[XTCR\\_C AutoCAD 2D Footprint \(mm\)](#)

[XTCR\\_C 2D PDF](#)

[XTCR\\_C 3D Inventor](#)

[XTCR\\_C AutoCAD 2D Footprint](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCR025C21A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton XTCR025C21A

Catalog Number: XTCR025C21A

Eaton XT IEC contactor, 25A, 110 Vac 50 Hz, 120 Vac 60 Hz, 2NO-2NO, 25A, Frame C, 45 mm, 50-60 Hz, 2, 5/ 7.5, 10, 15, 20 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Reversing, , Screw terminals, FVR

## General specifications



**Product Name**  
Eaton XT IEC contactor

**Catalog Number**  
XTCR025C21A

**UPC**  
786685180236

**Product Length/Depth**  
7.5 in

**Product Height**  
4.5 in

**Product Width**  
4.75 in

**Product Weight**  
2.45 lb

**Certifications**  
UL Listed

## Product specifications

### Amperage Rating

25A

### HP rating - max

2, 5/ 7.5, 10, 15, 20 hp (1/3PH @115,230/200,230,460,575 V)

### Number Of Poles

Three-pole

### Type

Full voltage reversing contactor

### Frequency rating

50-60 Hz

### Terminals

Screw terminals

### Coil voltage

110-120 Vac, 50/60 Hz

### Contact configuration

2 NO, 2 NO

### Continuous ampere rating

25 A

### Series

XT IEC

### Operation

Reversing

## Resources

### Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

### Drawings

[XTCR\\_C 3D Model Xchange](#)

[XTCR\\_C 2D Drawing Xchange](#)

[XTCR\\_C AutoCAD 2D Footprint \(mm\)](#)

[XTCR\\_C 2D PDF](#)

[XTCR\\_C 3D Inventor](#)

[XTCR\\_C AutoCAD 2D Footprint](#)

### Specifications and datasheets

[Eaton Specification Sheet - XTCR025C21A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)