Specifications







Eaton XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR

General specification	S
PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCR080F11A
UPC	782116356126
PRODUCT LENGTH/DEPTH	9.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	6.5 in
PRODUCT WEIGHT	4.7 lb
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified IEC 60947 EN 60947
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Product specifications	
AMPERAGE RATING	80A
HP RATING - MAX	7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
ТҮРЕ	Full voltage reversing contactor
FREQUENCY RATING	50-60 Hz
TERMINALS	Screw terminals
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	80 A
SERIES	XT IEC
OPERATION	Reversing

Resources	
CATALOGS	Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1
SPECIFICATIONS AND DATASHEETS	<u>Eaton Specification Sheet -</u> <u>XTCR080F11A</u>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

information.





latest product and support

Follow us on social media to get the





Specifications







Eaton XTCR080F11A

Eaton XT IEC contactor, 80A, Top-mounted, 110 Vac 50 Hz, 120 Vac 60 Hz, 1NO-1NC, 80A, Frame F, 90 mm, 50-60 Hz, 7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVR

General specification	S
PRODUCT NAME	Eaton XT IEC contactor
CATALOG NUMBER	XTCR080F11A
UPC	782116356126
PRODUCT LENGTH/DEPTH	9.5 in
PRODUCT HEIGHT	6 in
PRODUCT WIDTH	6.5 in
PRODUCT WEIGHT	4.7 lb
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Listed CSA Certified IEC 60947 EN 60947
CATALOG NOTES	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)



Product specifications	
AMPERAGE RATING	80A
HP RATING - MAX	7.5, 15/ 25, 30, 60, 75 hp (1/3PH @115,230/200,230,460,575 V)
NUMBER OF POLES	Three-pole
ТҮРЕ	Full voltage reversing contactor
FREQUENCY RATING	50-60 Hz
TERMINALS	Screw terminals
COIL VOLTAGE	110-120 Vac, 50/60 Hz
CONTACT CONFIGURATION	1 NO, 1 NC
CONTINUOUS AMPERE RATING	80 A
SERIES	XT IEC
OPERATION	Reversing

Resources	
CATALOGS	Motor Control and Protection, IEC Contactors and Starters, Volume 5, Tab 1
SPECIFICATIONS AND DATASHEETS	<u>Eaton Specification Sheet -</u> <u>XTCR080F11A</u>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

information.





latest product and support

Follow us on social media to get the



