



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA8CL4BOX 8AWG Alcu 1H Lug *Burndy LLC*

Catalog Number	YA8CL4BOX
Manufacturer	Burndy LLC
Description	8 Awg Cu, One Hole, 1/2 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Red Color Code, 49 Die Index.
Weight per unit	0.0002 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	49
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	RED
------------	-----

### Descriptions

Description	8AWG ALCU 1H LUG
extra long description	BUR YA8CL4BOX 8 STR CU 1-HOLE SHORT
Long Description	8 AWG CU, One Hole, 1/2 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, RED Color Code, 49 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 1/2 IN, Temperature Rating: 90 DEG C, Package: Box, Die Index: 49, Tongue Angle: Straight, Finish: Electro-Tin Plated, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W8CVT, W8CRT, X8CRT Die, (1), Hydraulic: BCT500HS, Y500CTHS Tool, W8CVT, W8CRT, X8CRT Die, (1), Y35, Y39, Y750, PAT750 Tool, U8CRT Die, (1), Y46 Tool, U8CRT Die With PUADP-1 Adapter, (1), Color

### Manufacturer Information

Brand	BURNDY
GTIN	00781810552445
Manufacturers Part Number	YA8CL4BOX
UPC	781810552445

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.0002

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B