

BURNDY Catalog Number YAEV10
UPC Number 7818100278066
Description 12-10 NYL. HVY DTY RING, #8-10 Stud
Status Active

Web Use
 BURNDY Product Line

Dimensional	
Length (in)	1.16
Tongue Type	Ring
Stud Size (in)	#10,#8
Pad Width (in)	0.37

Electrical	
Max Voltage Rating	600

General	
Product Description	Copper Terminal, Ring Tongue w/ Inspection Hole, Wire Range 12-10 AWG, #8-#10 Stud, Nylon Insulated, Short Barrel, Tin Plated, 600 Volts Max.

Conductor(s)	
Aircraft Cable Size (Range)	AN 12-AN 10
Copper Solid Size (Range)	N/A
Navy Cable Size (Range)	N/A
Copper Stranded (Range)	12-10

Physical	
Type of Plating	Tin
Connector Type	Terminal
Color Code	Yellow
Insulation Type	Nylon
Plated (Yes or No)	Y

Approvals / Certifications	
Industry Standards	Military Specified (Mil-Spec),UL486
UL Listed	Y
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation

For further technical assistance, please contact us



BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175



BURNDY Catalog Number
UPC Number

YAEV10
7818100278066

Description

12-10 NYL. HVY DTY RING, #8-10 Stud

Status

Active

Web Use

BURNDY Product Line

Dimensional

Length (in) 1.16
Tongue Type Ring
Stud Size (in) #10,#8
Pad Width (in) 0.37

Electrical

Max Voltage Rating 600

General

Product Description

Copper Terminal, Ring Tongue w/ Inspection Hole, Wire Range 12-10 AWG, #8-#10 Stud, Nylon Insulated, Short Barrel, Tin Plated, 600 Volts Max.

Conductor(s)

Aircraft Cable Size (Range) AN 12-AN 10
Copper Solid Size (Range) N/A
Navy Cable Size (Range) N/A
Copper Stranded (Range) 12-10

Physical

Type of Plating Tin
Connector Type Terminal
Color Code Yellow
Insulation Type Nylon
Plated (Yes or No) Y

Approvals / Certifications

Industry Standards Military Specified (Mil-Spec),UL486
UL Listed Y
CSA Certified N
ROHS Compatible Compliant
UL Recognized N
CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175