



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YAV4CL4 4AWG Heavy Duty Ring 5/16 Stud

Burndy LLC

Catalog Number	YAV4CL4
Manufacturer	Burndy LLC
Description	Copper Compression Lug, Ring Tongue, 1 Hole W/ Inspection Window, An 4 Flex, 5/16" Stud, Short Barrel, Electro-Tin Plated.
Weight per unit	0.0200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	40
Material	Copper
pallet quantity	79200

Material, Color, and Finish

material composition	DLP Copper;Tin Plating
----------------------	------------------------

Descriptions

Description	4AWG HEAVY DUTY RING 5/16 STUD
extra long description	BUR YAV4CL4 4AWG HVYDTY RING 5/16 S
Long Description	Copper Compression Lug, Ring Tongue, 1 Hole w/ Inspection Window, AN 4 Flex, 5/16" Stud, Short Barrel, Electro-Tin Plated.
Product Type	Terminal
Special Features	Features: HYLUG Type YAV Is A Seamless, Heavy Duty Uninsulated Compression Terminal Manufactured From Electrolytic Copper And Is For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, The Seamless Tubing Produces A Double Thick Tongue And Seamless Barrel Design Provides A Strong Connector For Demanding Applications Requiring High Reliability, Applications Include Aircraft, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To V

Manufacturer Information

Brand	BURNDY
GTIN	00781810025574
Manufacturers Part Number	YAV4CL4
UPC	781810025574

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Ring Tongue



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	200
Weight Per each	0.02

Uses, Certifications, and Standards

Application	Industrials, Hospitals, Utilities, Marine, Computer
standard	UL467;Military Specified (Mil-Spec)