



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YS1C #1 Butt Splice Long

Burndy LLC

Catalog Number	YS1C
Manufacturer	Burndy LLC
Description	1 Awg Cu, Long Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Green Color Code, 11 or 375 Die Index
Weight per unit	0.0600 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	11
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	GREEN
Finish	Tin-Plated

Descriptions

Description	#1 BUTT SPLICE LONG
extra long description	BUR YS1C BUTT SPLICE LONG 1
Long Description	1 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, GREEN Color Code, 11 or 375 Die Index
Product Type	Splice
Special Features	Features: UL Listed 90 DEG C, 600 Volts to 35 kV, Long Barrel Length: Ideal For 600 Volt Heavy Duty Applications, Also May Be Used At Higher Voltages Up To 35KV, Four (4) Center Conductor Stops: Provides A Center Wire Stop For Proper Conductor Insertion, High Pull Out Force: Provides Added Security For Much Greater Mechanical And Electrical Properties, Tapered End: No, Color Code: Green, Oil Stop: No, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Die Index: 11 Or 375, Tools,

Manufacturer Information

Brand	BURNDY
GTIN	00781810506905
Manufacturers Part Number	YS1C
UPC	781810506905

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS, Long Barrel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	20
Weight Per each	0.06

Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B