



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



YS30L 300MCM Butt Splice

Burndy LLC

Catalog Number	YS30L
Manufacturer	Burndy LLC
Description	300 Kcmil Cu, Standard Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, White Color Code, 17 or 298 Die Index.
Weight per unit	0.1400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Die Index	17
Material	Copper
Voltage Rating	35

Material, Color, and Finish

Color Code	WHITE
Finish	Tin-Plated

Descriptions

Description	300MCM BUTT SPLICE
extra long description	BUR YS30L 300 MCM CU. BUTT SPLICE
Long Description	300 kcmil CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, WHITE Color Code, 17 or 298 Die Index.
Product Type	Splice
Special Features	Features: Standard Barrel Length, Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops, Provides A Center Wire Stop For Proper Conductor Insertion, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD7-34R Tool, W30CVT Die, (2), Y35, Y39, Y750, Y46 Tool, U30CRT Die, (2), Die Index: 17 Element A, Color Code: White, Dieless Tools (number Of Crimps): Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (2), Wire Strip Length: 1-1/8 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810508152
Manufacturers Part Number	YS30L
UPC	781810508152

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS-L, Standard Barrel



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.14

Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B