



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YS8CLBOX #8 STR Cu Butt Splice

Burndy LLC

Catalog Number	YS8CLBOX
Manufacturer	Burndy LLC
Description	8 Awg Cu, Standard Barrel, Internal Chamfer, Tin Plated, UI/Csa, 90 C, Up to 35KV, Red Color Code, 49 Die Index.
Weight per unit	0.0110 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	49
Material	Copper
pallet quantity	60000
Voltage Rating	35

### Material, Color, and Finish

Color Code	RED
Finish	Tin-Plated

### Descriptions

Description	#8 STR CU BUTT SPLICE
extra long description	BUR YS8CLBOX 8 STR. CU. BUTT SPLICE
Long Description	8 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90 C, Up to 35kV, RED Color Code, 49 Die Index.
Product Type	Splice
Special Features	Features: Standard Barrel Length, Ideal For Limited Space Applications While Providing Ample Barrel Length For Proper Crimp, Four (4) Center Conductor Stops, Provides A Center Wire Stop For Proper Conductor Insertion, Conductor Type: Commercial Stranded Copper, Die Index: 49 Element A, Color Code: Red, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: Y1MRTC, Y2MR Tool, (1), MD7-34R Tool, W8CVT Die, (1), MD6, OUR840 Tool, X8CRT Die, (1), Y35, Y39, Y750, Y46 Tool, U8CRT Die, (1), Dieless To

### Manufacturer Information

Brand	BURNDY
GTIN	00781810022092
Manufacturers Part Number	YS8CLBOX
UPC	781810022092

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	YS-L, Standard Barrel



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	50
Weight Per each	0.011

## Uses, Certifications, and Standards

Application	Wire Splice
standard	UL 486A-486B