



**Southwire™**

TOOLS & EQUIPMENT

# 2018 CORD SOLUTIONS CATALOG



BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™

[SOUTHWIRETOOLS.COM](http://SOUTHWIRETOOLS.COM)

# OUR STORY

For over 60 years, Southwire has provided high quality electrical wire and cable to the commercial and industrial construction industries. Now, the name you trust provides durable, cutting-edge professional grade tools, designed with safety and productivity in mind. Look to Southwire® for solutions to all your electrical needs, from electrician's hand tools, meters, contractor equipment, temporary power, and extension cords.

## SOUTHWIRE, THE COMPANY

Southwire Company, LLC is North America's leading manufacturer of wire and cable used in the distribution and transmission of electricity. Throughout its history, our company has sought to help provide power through our products, our service and by helping empower our customers, employees and communities.

## SOUTHWIRE, THE PEOPLE

With more than 7,000 people at customer service centers, manufacturing facilities and sales offices throughout North America, we are dedicated to developing the highest-quality products and legendary service.

## THE DRIVE FOR EXCELLENCE

Driving for excellence starts with being responsive to our customers and the markets we serve. By creating divisions, Southwire Company enables each to foster an entrepreneurial spirit, innovative solutions and responsiveness required in today's business. At the same time each division can leverage the resources and rich history of Southwire Company as a whole.

## THE PRODUCTS

To be successful requires products that give you solutions no matter what stage of the project cycle you are in. Our product teams and dedicated resources work together to listen to and work with our customers, creating solutions that deliver unparalleled value through product innovation safety, and efficiency.

## THE SERVICE

Service is more than a word or a phone number, it's a tangible support system that assists you through the entire project cycle. Starting with our own knowledgeable customer service team, to our National Field Sales team, and our new District Merchandising Specialists. In the office or in the field, we're there to lend a hand, just when you need it most. 1-855-SWTOOLS (855-798-6657)



# TABLE OF CONTENTS

Polar/Solar® Supreme & Polar/Solar®.....	4
ColdFlex™ Cold Weather Cords.....	6
Royal® Welding Cords.....	7
Agripro™ Farm-Tough Cords.....	8
Outdoor Extension Cords.....	9
Heavy-Duty Outdoor Extension Cords.....	12
Specialty Extension Cords.....	13
Adapters.....	17
Cord Organization.....	19

# HOW TO ORDER

To order, please contact your Southwire Tools & Equipment sales representative.

# POLAR/SOLAR® SUPREME



Polar/Solar® Supreme extension cords are formulated to offer superior jobsite performance in extremely cold weather.

- Temperature Rating of -94°F to 221°F (-70°C to 105°C)
- 125 Voltage Rating
- Abrasion, chemical and oil resistant
- Common Applications: Cable Puller, Chop Saw, Rotary Hammer Drill

## SPECIFICATIONS

### OUTDOOR EXTENSION CORDS W/ POWER LIGHT INDICATOR



1638SW0061

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
1437SW0061	14/3	SJEOW	25'	7.6 m	Blue/White	15	12
1438SW0061	14/3	SJEOW	50'	15.2 m	Blue/White	15	6
1439SW0061	14/3	SJEOW	100'	30.5 m	Blue/White	13	6
1637SW0061	12/3	SJEOW	25'	7.6 m	Blue/White	15	12
1638SW0061	12/3	SJEOW	50'	15.2 m	Blue/White	15	6
1639SW0061	12/3	SJEOW	100'	30.5 m	Blue/White	15	4

POLAR SOLAR | CORDS

# POLAR/SOLAR®

Polar/Solar® extension cords are built to stay flexible under the most extreme temperatures.

- Temperature Rating of -58°F to 221°F (-50°C to 105°C)
- 125 Voltage Rating
- Abrasion, chemical and oil resistant
- Common Applications: Cable Puller, Chop Saw, Rotary Hammer Drill

## SPECIFICATIONS

### OUTDOOR EXTENSION CORDS



1628SW0008

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
1427SW0008	14/3	SJE00W	25'	7.6 m	Black	15	12
1428SW0008	14/3	SJE00W	50'	15.2 m	Black	15	6
1429SW0008	14/3	SJE00W	100'	30.5 m	Black	13	6
1628SW0008	12/3	SJE00W	50'	15.2 m	Black	15	6
1629SW0008	12/3	SJE00W	100'	30.5 m	Black	15	4



1688SW0002

## OUTDOOR EXTENSION CORDS W/ POWER LIGHT INDICATOR

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
1287SW0002	16/3	SJEOW	25'	7.6 m	Yellow	13	12
1288SW0002	16/3	SJEOW	50'	15.2 m	Yellow	13	12
1289SW0002	16/3	SJEOW	100'	30.5 m	Yellow	10	6
14840002	14/3	SJE00W	10'	3 m	Yellow	15	24
1487SW0002	14/3	SJE00W	25'	7.6 m	Yellow	15	12
1488SW0002	14/3	SJE00W	50'	15.2 m	Yellow	15	6
1489SW0002	14/3	SJE00W	100'	30.5 m	Yellow	13	6
1687SW0002	12/3	SJE00W	25'	7.6 m	Yellow	15	12
1688SW0002	12/3	SJE00W	50'	15.2 m	Yellow	15	6
1689SW0002	12/3	SJE00W	100'	30.5 m	Yellow	15	4
1787SW0002	10/3	SJE00W	25'	7.6 m	Yellow	15	6
1788SW0002	10/3	SJE00W	50'	15.2 m	Yellow	15	4
1789SW0002	10/3	SJE00W	100'	30.5 m	Yellow	15	3



1768SW0002

## HEAVY-DUTY OUTDOOR EXTENSION CORDS W/ POWER LIGHT INDICATOR

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
1567SW0002	14/3	SE00W	25'	7.6 m	Yellow	15	6
1568SW0002	14/3	SE00W	50'	15.2 m	Yellow	15	6
1569SW0002	14/3	SE00W	100'	30.5 m	Yellow	13	3
1767SW0002	12/3	SE00W	25'	7.6 m	Yellow	15	12
1768SW0002	12/3	SE00W	50'	15.2 m	Yellow	15	6
1769SW0002	12/3	SE00W	100'	30.5 m	Yellow	15	4



3488SW0002

## OUTDOOR TRITAP EXTENSION CORDS W/ POWER LIGHT INDICATOR

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
3482SW8802	12/3	SE0W	2'	0.6 m	Yellow	15	12
3487SW0002	12/3	SJE00W	25'	7.6 m	Yellow	15	12
3488SW0002	12/3	SJE00W	50'	15.2 m	Yellow	15	6
3489SW0002	12/3	SJE00W	100'	30.5 m	Yellow	15	4
3588SW0002	10/3	SJE00W	50'	15.2 m	Yellow	15	4
3589SW0002	10/3	SJE00W	100'	30.5 m	Yellow	15	3

CORDS | POLAR SOLAR

# COLDFLEX™ COLD WEATHER CORDS

ColdFlex™ extension cords withstand harsh, winter temperatures, and have a highly visible bright blue jacket to increase safety.

- Temperature Rating of -58°F to 140°F (-50°C to 60°C)
- 125 Voltage Rating
- Common Applications: Snow Thrower, Electric Chainsaw, Work Light

## SPECIFICATIONS

### OUTDOOR EXTENSION CORDS



2568SW0006

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
2367SW8806	16/3	ColdFlex SJTW	25'	7.6 m	Blue	13	12
2368SW8806	16/3	ColdFlex SJTW	50'	15.2 m	Blue	13	12
2436	16/3	ColdFlex SJTW	100'	30.5 m	Blue	10	6
2467SW8806	14/3	ColdFlex SJTW	25'	7.6 m	Blue	15	6
2468SW8806	14/3	ColdFlex SJTW	50'	15.2 m	Blue	15	6
2469SW8806	14/3	ColdFlex SJTW	100'	30.5 m	Blue	13	3
2437	12/3	ColdFlex SJTW	25'	7.6 m	Blue	15	12
2568SW0006	12/3	ColdFlex SJTW	50'	15.2 m	Blue	15	4
2569SW0006	12/3	ColdFlex SJTW	100'	30.5 m	Blue	15	4



32688806

### TRITAP EXTENSION CORDS W/ POWER LIGHT INDICATOR

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
32678806	14/3	ColdFlex SJTW	25'	7.6 m	Blue	15	6
32688806	14/3	ColdFlex SJTW	50'	15.2 m	Blue	15	6
41688806	12/3	ColdFlex SJTW	50'	15.2 m	Blue	15	6

# ROYAL<sup>®</sup> WELDING CORDS



Royal<sup>®</sup> extension cords are resistant to welding slag and are the most flexible extension cord on the market.

- Temperature Rating of -40°F to 194°F (-40°C to 90°C)
- 125 Voltage Rating
- Abrasion, chemical, and oil resistant
- Common Applications: Welder, Angle Grinder, Rotary Hammer Drill

## SPECIFICATIONS

### OUTDOOR EXTENSION CORDS W/ POWER LIGHT INDICATOR



3678SW0008

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
3677SW0008	12/3	SJ00W	25'	7.6 m	Black	15	12
3687SW0002	12/3	SJ00W	25'	7.6 m	Yellow	15	12
3678SW0008	12/3	SJ00W	50'	15.2 m	Black	15	6
3688SW0002	12/3	SJ00W	50'	15.2 m	Yellow	15	6
3679SW0008	12/3	SJ00W	100'	30.5 m	Black	15	4
3689SW0002	12/3	SJ00W	100'	30.5 m	Yellow	15	4

# AGRIPRO™ FARM-TOUGH CORDS

Agri-Pro™ extension cords are ideal for farm, ranch, and workshop jobs.

- Temperature Rating of -58°F to 221°F (-50°C to 105°C)
- 125 Voltage Rating
- Abrasion, chemical and oil resistant
- Common Applications: Air Compressor, Chop Saw, Electric Chain Saw

## SPECIFICATIONS

### EXTENSION CORDS

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
12270008	16/3	SJEOW	25'	7.6 m	Black	13	12
12280008	16/3	SJEOW	50'	15.2 m	Black	13	12
2457	12/3	SJTOW	50'	15.2 m	Black	15	4



12280008



2451

### TRITAP EXTENSION CORDS

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
54533501* **	14/3	SJOW	15'	4.6 m	Black	15	18
2451	14/3	SJTOW	25'	7.6 m	Black	15	12

\*Lighted Banana Receptacle

\*\*Product packaging is advertised in Meters



# OUTDOOR EXTENSION CORDS

Southwire outdoor extension cords are perfect for a variety of outdoor applications. These cords come in a variety of colors to increase visibility and prevent jobsite loss.

- Temperature rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Electric Push Mower, Pressure Washer, Electric Drill

## SPECIFICATIONS

### EXTENSION CORDS

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
22078803	16/2	SJTW	25'	7.6 m	Orange	13	12
22098803	16/2	SJTW	100'	30.5 m	Orange	10	6
2211SW8808	16/3	SJOW	10'	3 m	Black	13	24
2304SW8803	16/3	SJTW	10'	3 m	Orange	13	24
2306SW8808	16/3	SJTW	15'	4.6 m	Black	13	18
2305SW8803	16/3	SJTW	15'	4.6 m	Orange	13	18
2307SW8803	16/3	SJTW	25'	7.6 m	Orange	13	12
2308SW8803	16/3	SJTW	50'	15.2 m	Orange	13	12
2309SW8803	16/3	SJTW	100'	30.5 m	Orange	10	6
2407SW8804	14/3	SJTW	25'	7.6 m	Red	15	12
2408SW8804	14/3	SJTW	50'	15.2 m	Red	15	6
2409SW8804	14/3	SJTW	100'	30.5 m	Red	13	6
517	10/3	SJTW	50'	15.2 m	Orange	15	2
26188802^+	10/3	SJTOW	50'	15.2 m	Yellow	20	2
518	10/3	SJTW	100'	30.5 m	Orange	15	2

^5-20 P/R +LE Receptacle



2304SW8803



26188802



2488SW8804



541901



2577SW000H



2577SW000X



547703

## EXTENSION CORDS W/ POWER LIGHT INDICATOR

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
540836**	14/3	STW	3'	0.9 m	Red/Black	15	12
541901**	14/3	SJTW	22'	7 m	Red/Black	15	6
2487SW8804	14/3	SJTW	25'	7.6 m	Red	15	12
2488SW8804	14/3	SJTW	50'	15.2 m	Red	15	6
541902**	14/3	SJTW	50'	15.2 m	Red/Black	15	5
54800401**	14/3	SJTW	50'	15.2 m	Neon Pink	13	13
521*	14/3	SJTW	50'	15.2 m	Yellow/Black	15	13
2489SW8804	14/3	SJTW	100'	30.5 m	Red	13	6
541909**	14/3	SJTW	100'	30.5 m	Red/Black	15	3
2577SW000H	12/3	SJTW	25'	7.6 m	Cool Blue	15	12
2577SW000X	12/3	SJTW	25'	7.6 m	Cool Green	15	12
547703**	12/3	SJTW	25'	7.6 m	Dark Green/Yellow	15	12
2577SW000A	12/3	SJTW	25'	7.6 m	Cool Pink	15	12
2587SW8802	12/3	SJTW	25'	7.6 m	Yellow	15	12
2578SW000H	12/3	SJTW	50'	15.2 m	Cool Blue	15	8
2548SW0064	12/3	SJTW	50'	15.2 m	Cool Blue/Red	15	8
2548SW00HX	12/3	SJTW	50'	15.2 m	Cool Blue/Cool Green	15	8
2548SW0052	12/3	SJTW	50'	15.2 m	Dark Green/Yellow	15	8
2548SW0054	12/3	SJTW	50'	15.2 m	Lime Green/Red	15	8
2578SW000X	12/3	SJTW	50'	15.2 m	Cool Green	15	8
2548SW003V	12/3	SJTW	50'	15.2 m	Cool Orange/Cool Blue	15	8
2578SW000A	12/3	SJTW	50'	15.2 m	Cool Pink	15	8
2548SW0077	12/3	SJTW	50'	15.2 m	Cool Pink/Lime Green	15	8
2548SW0041	12/3	SJTW	50'	15.2 m	Red/White	15	8
2588SW0002	12/3	SJTW	50'	15.2 m	Yellow	15	8
2548SW0022	12/3	SJTW	50'	15.2 m	Yellow/Purple	15	8
550523**	12/3	SJTW	50'	15.2 m	Yellow/Black	15	6
25850002	12/3	SJTW	80'	24.4 m	Yellow	15	4
2549SW0064	12/3	SJTW	100'	30.5 m	Cool Blue/Red	15	4
2579SW000H	12/3	SJTW	100'	30.5 m	Cool Blue	15	4
2549SW0054	12/3	SJTW	100'	30.5 m	Lime Green/Red	15	4
2579SW000X	12/3	SJTW	100'	30.5 m	Cool Green	15	4
2549SW0052	12/3	SJTW	100'	30.5 m	Dark Green/Yellow	15	4
2549SW003V	12/3	SJTW	100'	30.5 m	Cool Orange/Cool Blue	15	4
2549SW0077	12/3	SJTW	100'	30.5 m	Cool Pink/Lime Green	15	4
2579SW000A	12/3	SJTW	100'	30.5 m	Cool Pink	15	4
2549SW0041	12/3	SJTW	100'	30.5 m	Red/White	15	4
2549SW0022	12/3	SJTW	100'	30.5 m	Yellow/Purple	15	4
2589SW0002	12/3	SJTW	100'	30.5 m	Yellow	15	4
2687SW0002	10/3	SJTW	25'	7.6 m	Yellow	15	6
26480064	10/3	SJTW	50'	15.2 m	Cool Blue/Red	15	4
26480054	10/3	SJTW	50'	15.2 m	Lime Green/Red	15	4
2688SW0002	10/3	SJTW	50'	15.2 m	Yellow	15	4
26490064	10/3	SJTW	100'	30.5 m	Cool Blue/Red	15	3
26490054	10/3	SJTW	100'	30.5 m	Lime Green/Red	15	3
2689SW0002	10/3	SJTW	100'	30.5 m	Yellow	15	3

\*Black Plugs

\*\*Product packaging is advertised in Meters



2548SWUSA1

## RED, WHITE, AND BLUE EXTENSION CORDS W/ POWER LIGHT INDICATOR

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
2547SWUSA1	12/3	SJTW	25'	7.6 m	Red/White/Blue	15	12
2548SWUSA1	12/3	SJTW	50'	15.2 m	Red/White/Blue	15	8
2549SWUSA1	12/3	SJTW	100'	30.5 m	Red/White/Blue	15	4



4004SW8803

## TRITAP EXTENSION CORDS

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
4004SW8803	14/3	SJTW	6'	1.8 m	Orange	15	18
4217SW8804	14/3	SJTW	25'	7.6 m	Red	15	12
4218SW8804	14/3	SJTW	50'	15.2 m	Red	15	6
4219SW8804	14/3	SJTW	100'	30.5 m	Red	13	6
4112SW8802	12/3	STW	2'	0.6 m	Yellow	15	12
19100002*	12/3	SJTW	25'	7.6 m	Yellow	15	12

\*Black Plugs



4188SW8802

## TRITAP EXTENSION CORDS W/ POWER LIGHT INDICATOR

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
540835**	14/3	STW	3'	0.9 m	Red	15	6
4187SW8802	12/3	SJTW	25'	7.6 m	Yellow	15	12
4188SW8802	12/3	SJTW	50'	15.2 m	Yellow	15	6
4189SW8802	12/3	SJTW	100'	30.5 m	Yellow	15	4
4388SW8802	10/3	SJTW	50'	15.2 m	Yellow	15	4
4389SW8802	10/3	SJTW	100'	30.5 m	Yellow	15	3

\*\*Product packaging is advertised in Meters

# HEAVY-DUTY OUTDOOR EXTENSION CORDS

Southwire heavy-duty extension cords have a thicker jacket than standard outdoor cords to withstand common jobsite wear and tear.

- Temperature rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Table Saw, Heat Gun, Work Light



2558SW0003

## SPECIFICATIONS

### OUTDOOR EXTENSION CORDS

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
2457SW0003	14/3	STW	25'	7.6 m	Orange	15	6
2458SW0003	14/3	STW	50'	15.2 m	Orange	15	4
2459SW0003	14/3	STW	100'	30.5 m	Orange	13	3
2557SW0003	12/3	STW	25'	7.6 m	Orange	15	6
2558SW0003	12/3	STW	50'	15.2 m	Orange	15	4
2559SW0003	12/3	STW	100'	30.5 m	Orange	15	3



3130

### MULTI-OUTLET EXTENSION CORDS

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
90028802*	14/3	STW	6'	1.8 m	Yellow	15	6
3130	14/3	STW	9'	2.7 m	Black	15	4
90018802	14/3	STW	25'	7.6 m	Yellow	15	4

\*Black Plugs

# SPECIALTY EXTENSION CORDS

Southwire has a variety of specialty extension cords to meet a variety of indoor and outdoor needs.

## SPECIFICATIONS



24388826

### PUSH-LOCK EXTENSION CORDS

Southwire push-lock extension cords keep your tools plugged in while doing common yard work.

- Temperature rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Electric Push Mower, Leaf Blower, Hedge Trimmer

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
24388826	14/3	SJTW	50'	15.2 m	Yellow/Blue	15	4
24398826	14/3	SJTW	100'	30.5 m	Yellow/Blue	13	3
25388828	12/3	SJTW	50'	15.2 m	Yellow/Black	15	4



9029SW8802

### TWIST-TO-LOCK EXTENSION CORDS

Southwire twist-to-lock extension cords are designed to keep your jobsite under continuous operation.

- Temperature rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Generator, Pool Pump
- NEMA L5-20P

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
9208SW8802	12/3	SJTW	50'	15.2 m	Yellow	20	6
90288802*	12/3	STW	50'	15.2 m	Yellow	20	4
9209SW8802*	12/3	SJTW	100'	30.5 m	Yellow	15	4
9029SW8802*	12/3	STW	100'	30.5 m	Yellow	15	3
92390008*	12/3	SE00W	100'	30.5 m	Black	15	3

\*Black Plugs



9044SW8808

## RANGE AND DRYER CORDS

- Temperature rating of -4°F to 140°F (-20°C to 60°C)
- 125/250 Voltage Rating

Stock #	Gauge/ Conductors	Wire Type	Number of Wires	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity	NEMA Plug	NEMA Receptacle
9014SW8809	6/2-8/1	SRDT Flat	3	4'	1.2 m	Gray	50	6	10-50P	
9016SW8809	6/2-8/1	SRDT Flat	3	6'	1.8 m	Gray	50	6	10-50P	
9044SW8808	6/2-8/2	SRDT Round	4	4'	1.2 m	Black	50	6	14-50P	
9046SW8808	6/2-8/2	SRDT Round	4	6'	1.8 m	Black	50	6	14-50P	
544094**	8/2-10/2	DRT		5'	1.5 m	Black	40	8	14-50P	
544147**	8/2-10/2	DRT		5'	1.5 m	Black	40	15	14-50P	
544120* **	10/2	DRT		5'	1.5 m	Black	30	8	14-30P	
9124SW8809	10/3	SRDT Flat	3	4'	1.2 m	Gray	30	6	10-30P	
9126SW8809	10/3	SRDT Flat	3	6'	1.8 m	Gray	30	6	10-30P	
9154SW8808	10/4	SRDT Round	4	4'	1.2 m	Black	30	6	14-30P	
9156SW8808	10/4	SRDT Round	4	6'	1.8 m	Black	30	6	14-30P	
9042SW8801						White	15	4	14-50P	5-15R

\*CSA (Canadian Standards Association)

\*\*Product packaging is advertised in Meters



9042SW8801



9858SW0008

## GARAGE & WORKSHOP REPLACEMENT POWER SUPPLY CORDS

- Temperature rating of:
  - SJEOW -58°F to 221°F (-50°C to 105°C)
  - SJT -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Electric Trimmer, Electric Chainsaw, Air Compressor

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
9853SW0008	16/2	SJEOW	6'	1.8 m	Black	13	50
9854SW0008	16/2	SJEOW	9'	2.7 m	Black	13	50
98388808	16/3	SJT	2.5'	0.7 m	Black	13	100
9855SW0008	16/3	SJEOW	6'	1.8 m	Black	13	50
9856SW0008	16/3	SJEOW	9'	2.7 m	Black	13	50
9857SW0008	14/3	SJEOW	6'	1.8 m	Black	15	25
9858SW0008	14/3	SJEOW	9'	2.7 m	Black	15	25
90110008	12/3	SE00W	2'	0.6 m	Black	15	50
90120008	12/3	SE00W	2'	0.6 m	Black	15	50



9716SW8808

## INDOOR REPLACEMENT ROUND POWER SUPPLY CORDS

- Temperature Rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Vacuum, Electric Drill, Work Light

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
9702SW8808	16/2	SJTW	6'	1.8 m	Black	13	25
9703SW8808	16/3	SJTW	3'	0.9 m	Black	13	25
9706SW8808	16/3	SJTW	6'	1.8 m	Black	13	25
9709SW8808	16/3	SJTW	9'	2.7 m	Black	13	25
9716SW8808	14/3	SJTW	6'	1.8 m	Black	15	25
9719SW8808	14/3	SJTW	9'	2.7 m	Black	15	25



9734SW8809

## INDOOR REPLACEMENT FLAT POWER SUPPLY CORDS

- Temperature Rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Microwave, Refrigerator, Dehumidifier

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
9723SW8809	16/3	SPT-3	3'	0.9 m	Gray	13	25
9733SW8809	16/3	SPT-3 Straight	3'	0.9 m	Gray	13	25
9724SW8809	16/3	SPT-3 R/Angle	4'	1.2 m	Gray	13	25
9734SW8809	16/3	SPT-3 Straight	4'	1.2 m	Gray	13	25
9726SW8809	16/3	SPT-3 R/Angle	6'	1.8 m	Gray	13	25
9736SW8809	16/3	SPT-3 Straight	6'	1.8 m	Gray	13	25
9743SW8823	14/3	SPT-3 Straight	3'	0.9 m	Beige	15	25
9743SW09	14/3	SPT-3 Straight	3'	0.9 m	Gray	15	25
9746SW8823	14/3	SPT-3 Straight	6'	1.8 m	Beige	15	25
98700009	12/3	SPT-3	6'	1.8 m	Beige	15	25



3533SW3323

## INDOOR MAJOR APPLIANCE REPLACEMENT CORDS

- Temperature Rating of -4°F to 140°F (-20°C to 60°C)
- 125 Voltage Rating (250 Voltage Rating for 3537SW8809)
- Common Applications: Air Conditioner, Space Heater, Refrigerator

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
3531SW3323	14/3	SPT-3	3'	0.9 m	Beige	15	36
3531SW09	14/3	SPT-3	3'	0.9 m	Gray	15	24
3532SW3323	14/3	SPT-3	6'	1.8 m	Beige	15	24
3532SW09	14/3	SPT-3	6'	1.8 m	Gray	15	24
3533SW3323	14/3	SPT-3	9'	2.7 m	Beige	15	18
3535SW3323	14/3	SPT-3	12'	3.7 m	Beige	15	12
3536SW3323	14/3	SPT-3	15'	4.6 m	Beige	15	12
3537SW8809*	12/3	SPT-3	9'	2.7 m	Gray	20	18

\*6-20 P/R



98130008

## COILED CORDS

- Temperature Rating of -58°F to 194°F (-50°C to 90°C)
- 300 Voltage Rating (SJEOW)
- 600 Voltage Rating (SEOW & SEOW)

Stock #	Gauge/Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Case Pack Quantity
98090008	18/2	SJEOW	4-20'	1.2-6 m	Black	10
98100008	18/3	SJEOW	4-20'	1.2-6 m	Black	12
98110008	18/4	SJEOW	4-20'	1.2-6 m	Black	10
98120008	16/2	SJEOW	4-20'	1.2-6 m	Black	10
98130008	16/3	SJEOW	4-20'	1.2-6 m	Black	10
98140008	16/4	SJEOW	4-20'	1.2-6 m	Black	10
98150008	14/3	SEOW	4-20'	1.2-6 m	Black	5
98160008	12/3	SEOW	4-20'	1.2-6 m	Black	5



# ADAPTERS

Southwire offers a variety of adapters for generators, converting receptacles or outlets for multiple uses.

\*Product images displayed on following page

## SPECIFICATIONS

### GENERATOR ADAPTERS W/ LIGHTED END

Southwire generator adapters provide more usable receptacles during temporary power outages and on jobsites.

- Temperature Rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity	NEMA Plug	NEMA Receptacle
19158802	10/3	STOW	3'	0.9 m	Black	15	4	L5-30P	5-20R
19348802	10/4	STOW	3'	0.9 m	Black	20	4	L14-30P	5-20R
19248802	12/4	STOW	3'	0.9 m	Black	20	4	L14-20P	5-20R

### TWIST-TO-LOCK ADAPTERS

Southwire twist-to-lock adapters easily convert plugs and receptacles to fit your specific application.

- Temperature Rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Generator, Pool Pump

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity	NEMA Plug	NEMA Receptacle
90208802	12/3	STW	9"	0.2 m	Yellow	15-20	10	5-15P	L5-20R
90218802	12/3	STW	9"	0.2 m	Yellow	15-20	10	L5-20P	5-15R
90228802	12/3	STW	20"	0.5 m	Yellow	20	10	L5-20P	L5-20R x2
90238802	12/3	STW	2'	0.6 m	Yellow	20	10	L5-20P	L5-20R x3
90848802+^	12/3	STW	2'	0.6 m	Yellow	15	6	L5-20P	5-15R x3

+Tritap

^Lighted Receptacle


### ADAPTERS

Southwire adapters transform your single outlet into multiple outlets.

- Temperature Rating of -40°F to 140°F (-40°C to 60°C)
- 125 Voltage Rating
- Common Applications: Generator, RV

Stock #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
90188802*	12/3	STW	2'	0.6 m	Yellow	15	12
90198802*	12/3	STW	2'	0.6 m	Yellow	15	12

\*Black Plugs



19158802



19348802



19248802



90208802



90218802



90228802



90238802



90848802



90188802



90198802

# CORD ORGANIZATION

Southwire's cord organization options for keeping bulky extension cords, ropes, and holiday lighting tangle free.

\*Product images displayed on following page

## SPECIFICATIONS

### CORD STORAGE WRAPS

Part #	Holds	Color	Case Pack Quantity
3202*	100' of 14/3 Gauge Cord	Yellow	10
247737^	50' of 14/3 Gauge Cord	Black	3

\*with Stand ^with 3 Outlets

### CORD STORAGE REEL

Part #	Holds	Color	Case Pack Quantity
E230*	50' of 12/3 Gauge Cord	Black/Yellow	4

\*with Metal Stand

### CORD REELS W/ LIGHTED ENDS

Part #	Gauge/Conductors	Wire Type	Color	Length (ft)	Length (m)	Outlets	Amps	Case Pack Quantity
E235	14/3	SJTW	Red/Black/Yellow	50'	15.2 m	6	15	2
445825**	14/3	SJTW	Black	50'	15.2 m	3	15	3
E238	12/3	SJTW	Green/Black/Yellow	50'	15.2 m	6	15	2

\*\*Product packaging is advertised in Meters

### RETRACTABLE CORD REELS W/ LIGHTED TRITAP

Part #	Gauge/Conductors	Wire Type	Color	Length (ft)	Length (m)	Outlets	Amps	Case Pack Quantity
E215^	16/3	SJTW	Silver/Black	30'	9.1 m	3	13	2
48006SW*	14/3	SJTW	Red/Black	30'	9.1 m	3	15	3
E316	14/3	SJTW	Green/Black	45'	13.7 m	3	15	2
48208802SW	12/3	SJTW	Black/Yellow	50'	15.2 m	3	15	1

\*Black End ^Banana Plug

### RETRACTABLE CORD REEL W/ WORK LIGHT

Part #	Gauge/Conductors	Wire Type	Color	Length (ft)	Length (m)	Outlets	Amps	Case Pack Quantity
48000	16/3	SJTW	Red/Black	40'	12.1 m	1	13	3

### RETRACTABLE CORD REEL W/ LOCKING PLUG

Part #	Gauge/Conductors	Wire Type	Color	Length (ft)	Length (m)	Outlets	Amps	Case Pack Quantity
48004	14/3	SJTW	Red/Black	30'	9.1 m	1	15	3

### INDUSTRIAL RETRACTABLE CORD REELS

Part #	Gauge/Conductors	Wire Type	Color	Length (ft)	Length (m)	Outlets	Amps	Case Pack Quantity	NEMA Plug	NEMA Receptacle
R112318845	12/3	SJEOW	Yellow/Black	45'	13.7 m	1	20	1	5-20P	5-20R
R112718845*	12/3	SJEOW	Yellow/Black	45'	13.7 m	2	20	1	5-20P	5-20R
R112308845	12/3	SJEOW	Yellow/Black	45'	13.7 m	1	15	1	5-15P	5-15R

\*with GFCI



3202



247737



E230



E235



445825



E238



E215



48006SW



E316



48208802SW



48000



48004



R112318845




R11271884



R112308845







**Southwire™**

TOOLS & EQUIPMENT

# 2018 CORD SOLUTIONS CATALOG

**GET SOCIAL WITH US:**



**/SOUTHWIRETOOLS  
/SOUTHWIRETOOLSLATINO**



**@SOUTHWIRETOOLS**



**@SOUTHWIRETOOLS**



**SOUTHWIRETOOLS**

**SOUTHWIRETOOLS.COM | 1-855-SWTTOOLS**

Delrin® is a registered trademark of E. I. du Pont de Nemours and Company of its affiliates for its brand of acetal resin.  
Milwaukee, Super Hawg, Hole Hawg are trademarks, service marks, or trade names of Milwaukee Electric Tool Corporation ("Milwaukee Electric Tool Corporation's Intellectual Property").  
All other Trademarks or Registered Trademarks (TM/®) are owned or licensed by Southwire Company.  
Any other ™/®- Trademark or Registered Trademark of Southwire Company.