



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1830 Barnett Drive
76087-0000, TX Weatherford
Phone: 817-599-7964
Fax: 817-599-8289



CHFQ130 3/4" Thermal MCB, Type CHFQ 3/4-Inch, 15a *Eaton Corp*

Catalog Number	CHFQ130
Manufacturer	Eaton Corp
Description	Eaton 3/4" Thermal Magnetic Circuit Breakers, Type CHFQ 3/4-Inch, 120/240V, #14-8, (2) #14-10 Awg Cu/Al, Type CH Loadcenters, 30 A, 10 Kaic, Single-Pole
Weight per unit	N/A
Product Category	20250930080902

Descriptions

Description	3/4" THERMAL MCB,TYPE CHFQ 3/4-INCH, 15A
Features	Eaton UL classified replacement circuit breakers are available in both 3/4-inch Type CHQ and 1-inch Type CL, single- and two-pole configurations. These breakers are classified as direct replacements by Underwriters Laboratories. In addition to a UL listing, they also come with a 15-year warranty.
Long Description	Eaton 3/4" Thermal magnetic circuit breakers,Type CHFQ 3/4-Inch, 120/240V, #14-8, (2) #14-10 AWG Cu/Al,Type CH Loadcenters, 30 A,10 kAIC,Single-pole
Product Type	3/4" Thermal MCB, Type CHFQ 3/4-Inch, 30a

Manufacturer Information

Brand	Eaton
GTIN	00629113000105
Manufacturers Part Number	CHFQ130
UPC	629113000105

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Packaging

Carton	1
Weight Per each	0