



Pass and Seymour
Tamper-Resistant Floor Box Assembly - One Gang for Wood Sub-Floor
Part No. FB1TRSRN



Tamper-Resistant Floor Box Assembly, Single Threaded screw plug. Includes 15A 125A tamper-resistant single receptacle. Nickel. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.	Rugged diecast cover plates.
Meets UL514(c) and NEC 314.27(c).	Scrub water compliant.
With durable nickel or brass cover plates.	Dual-voltage models available.
Swing brackets mounting option eliminates drilling tile flooring for mounting screws.	Wood sub-floors only.
Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.	

Specifications

General Info

Product Line	Pass & Seymour	Color	Nickel
UPC Number	785007108774	Country Of Origin	United States
Material	Thermoplastic	Features	Durable
Installation Location	Underfloor	Application Sector	Commercial, Residential
Standard	Residential/Commercial	Warranty Type	1-Year Limited Warranty
Type	Floor Box		

Dimensions

Product Width US	3.25 in	Product Depth US	4.0 in
Product Length US	4.75 in	Cubic Capacity	20.5 in ³

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back	Box Shape	Rectangular
Mounting Type	Screw Mount		
