



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GCL30 4 Sol-300 Kcmil GRD Clamp *Burndy LLC*

Catalog Number	GCL30
Manufacturer	Burndy LLC
Description	Cast Copper Alloy Ground Clamp, 4 STR. - 300, Cable to Bar.
Weight per unit	0.5550 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	COPPER ALLOY
pallet quantity	4536

Descriptions

Description	4 SOL-300 KCMIL GRD CLAMP
extra long description	BUR GCL30 4 Sol-300 Kcmil GRD CLAMP
Long Description	Cast Copper Alloy Ground Clamp, 4 Str. - 300, Cable to Bar.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Wide Range Of Two Parallel Cables To 1/4 IN Thick Bar, Type GC Separates Cable From Bar, One-Wrench Installation, UL467 Listed, The High Copper Alloy Cast Body And DURIUM Bolts, Nuts, And Lockwashers Make The GC For Direct Burial In Concrete Or Ground, Width: 1 IN, Height: 2 IN, Bar Thickness: 1/4 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810079478
Manufacturers Part Number	GCL30
UPC	781810079478

Taxonomies, Classifications, and Categories

Category Description	MISC FITTINGS
Type	GC

Packaging

Carton	1
Package	12
Weight Per each	0.555

Uses, Certifications, and Standards

Application	For Two Copper Cables To Bar And Direct Burial In Concrete Or Ground
standard	TAA Compliant (All status valid till December 2024)