



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3440 Hwy 114 Suite 200  
76177-0000, TX Fort Worth  
Phone: 682-237-5470  
Fax: 682-237-5471



## **GHB2100 Type GHB Breakr 2P 100A 277/480VAC Max 125/250VDC** *Eaton Corp*

|                  |                                                                                                                                                                                    |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | GHB2100                                                                                                                                                                            |
| Manufacturer     | Eaton Corp                                                                                                                                                                         |
| Description      | Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 100 A, 480Y/277 Vac, 125/250 VDC, 50/60 HZ |
| Weight per unit  | 1.2 (lbs/each)                                                                                                                                                                     |
| Product Category | 2 Pole                                                                                                                                                                             |

### **Features**

|                  |                                           |
|------------------|-------------------------------------------|
| Current Rating   | 100 A                                     |
| dimensions       | 2.6300 IN X 2.0000 IN X 4.0000 IN         |
| frame            | G                                         |
| interrupt rating | 65 kAIC at 240 Vac14 kAIC at 480Y/277 Vac |
| Poles            | Two-pole                                  |
| Trip Type        | T186                                      |
| Voltage Rating   | 480Y/277 Vac, 125/250 Vdc                 |

### **Descriptions**

|                        |                                                                                                                                                                                                                                                                                                                                                                                                           |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | TYPE GHB BREAKR 2P 100A 277/480VAC MAX 125/250VDC                                                                                                                                                                                                                                                                                                                                                         |
| extra long description | ETN GHB2100 GHB CCB 2P100A 277/480V                                                                                                                                                                                                                                                                                                                                                                       |
| Features               | Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A. |
| Long Description       | Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 100 A, 480Y/277 Vac, 125/250 Vdc, 50/60 Hz                                                                                                                                                                                                                        |
| Product Type           | GHB CCB 2P100A 277/480VAC Max 125/250VDC                                                                                                                                                                                                                                                                                                                                                                  |

### **Manufacturer Information**

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786679911242 |
| Manufacturers Part Number | GHB2100        |
| UPC                       | 786679911242   |

### **Taxonomies, Classifications, and Categories**

|                      |                             |
|----------------------|-----------------------------|
| Category Description | PANELBOARD BRANCH BREAKERS  |
| Type                 | Molded case circuit breaker |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3440 Hwy 114 Suite 200  
76177-0000, TX Fort Worth  
Phone: 682-237-5470  
Fax: 682-237-5471

## Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

## Packaging

|        |   |
|--------|---|
| Carton | 1 |
|--------|---|

|                 |      |
|-----------------|------|
| Weight Per each | 1.15 |
|-----------------|------|

## Uses, Certifications, and Standards

|             |                                                                           |
|-------------|---------------------------------------------------------------------------|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies and<br>OEMs - Other |
|-------------|---------------------------------------------------------------------------|

|                  |          |
|------------------|----------|
| Frequency Rating | 50/60 Hz |
|------------------|----------|

|          |                                                         |
|----------|---------------------------------------------------------|
| standard | UL Listed,Federal Specifications Classification W-C375B |
|----------|---------------------------------------------------------|