



Food Grade Belt Dressing, 10 Wt Oz

No. 03065 | Item# 1003326 | Case# 1003325

Product Description	A Food Grade Belt Dressing to extend the life of drive belts by improving traction & allowing runs under reduced belt tension.
Applications	Industrial machinery, conveyor systems, portable motorized equipment and vehicle belts.
Unit Package Description	16 Ounce Aerosol
Brand	CRC
Generic Description 1	Food Grade Synthetic Lubricant with Perma-Lock®
Net Fill	10 Wt Oz
UPC Code	078254030654
Unit Dimensions	7.75H x 2.63W x 2.63D in
Units Per Case	12
Case Dimensions	8.1H x 8.3W x 11.1D in
Cases Per Pallet	133
Case Weight	11 lbs
1 2 of 5 Code	30078254030655
Appearance	Light Amber Liquid
Base Type	Polyisobutene
Flash point (F)	<0°F
Flash point (C)	<-18°C
Flammability Class - CPSC	Extremely Flammable
Spec Gravity Concentrate	0.6783
Plastic Safe	Yes
Film Type	Tacky, Colorless, Non-Drying
Evaporation Rate	Fast
Dielectric Strength	26,600 Volts/Mil
Working Temp (F)	350°F (Continuous) / 400°F (Intermittent)
Working Temp (C)	176.7°C (Continuous) 204.4°C (Intermittent)
Propellant	Hydrocarbon

Last revised: 9/5/2019

Page 1 of 2



Chemical Solutions to Keep You Moving™

f t y d in • 800-272-8963 • crcindustries.com



NSF Category Code	H1
NSF Number	017386
Aerosol Flammability Level	III
DOT Proper Shipping Name	Aerosols, Flammable, Limited Quantity
VOC % (Consumer Product def)	92.8
VOC g/L (Consumer Product def)	628
VOC lbs/gal (Consumer Prod def)	5.24
VOC Category	Not Regulated
Removal (How To)	Remove with mineral spirits or HF™ Contact Cleaner.



Food Grade Belt Dressing, 10 Wt Oz

No. 03065 | Item# 1003326 | Case# 1003325

Product Description	A Food Grade Belt Dressing to extend the life of drive belts by improving traction & allowing runs under reduced belt tension.
Applications	Industrial machinery, conveyor systems, portable motorized equipment and vehicle belts.
Unit Package Description	16 Ounce Aerosol
Brand	CRC
Generic Description 1	Food Grade Synthetic Lubricant with Perma-Lock®
Net Fill	10 Wt Oz
UPC Code	078254030654
Unit Dimensions	7.75H x 2.63W x 2.63D in
Units Per Case	12
Case Dimensions	8.1H x 8.3W x 11.1D in
Cases Per Pallet	133
Case Weight	11 lbs
1 2 of 5 Code	30078254030655
Appearance	Light Amber Liquid
Base Type	Polyisobutene
Flash point (F)	<0°F
Flash point (C)	<-18°C
Flammability Class - CPSC	Extremely Flammable
Spec Gravity Concentrate	0.6783
Plastic Safe	Yes
Film Type	Tacky, Colorless, Non-Drying
Evaporation Rate	Fast
Dielectric Strength	26,600 Volts/Mil
Working Temp (F)	350°F (Continuous) / 400°F (Intermittent)
Working Temp (C)	176.7°C (Continuous) 204.4°C (Intermittent)
Propellant	Hydrocarbon

Last revised: 9/5/2019

Page 1 of 2



Chemical Solutions to Keep You Moving™

f t y d in • 800-272-8963 • crcindustries.com

CRC Industries, Inc. is a global leader in the production of specialty chemicals for maintenance, repair and operational professionals and do-it-yourselfers serving the automotive, industrial, electrical, marine, heavy truck, hardware and aviation markets. CRC trademarked brands include: CRC®, K&W®, Sta-Lube®, SmartWasher®, Marykate®, Weld-Aid®, Ambersil®, KF®, Kontakt Chemie®, Ados®, Action Can®, and Kitten®.

©2019 CRC Industries, Inc.



NSF Category Code	H1
NSF Number	017386
Aerosol Flammability Level	III
DOT Proper Shipping Name	Aerosols, Flammable, Limited Quantity
VOC % (Consumer Product def)	92.8
VOC g/L (Consumer Product def)	628
VOC lbs/gal (Consumer Prod def)	5.24
VOC Category	Not Regulated
Removal (How To)	Remove with mineral spirits or HF™ Contact Cleaner.