Pass and Seymour
Tamper-Resistant Floor Box Brass Cover
Part No. TM1542TRCF

High-profile Brass Cover, fits any floor finish - including carpeting, linoleum, tile floors includes 885 15A, 125A Decorator Duplex receptacle and will accept any decorator device. Cover includes captive screws to prevent loss.For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Tamper-Resistant shutters let plugs in, keep other things out.
- Standard Decorator opening that accepts GFCI, TVSS, DataCom, or other Decorator devices.
- Meets UL514(c) scrub water exclusion test.
- Simple mounting box, fits into a 4 3/4 inch hole and mounts with 3 screws included.
- UL and cUL Listed. Captive screws on TM1542 Series -- screws will not be lost -- new.
- Durable construction, impact, and scratch resistant PVC construction.
- Auto/Clamps and knockouts on both sides of box.
- Threaded device mounting holes.
- Ready for low-voltage wiring, drill guides on underside of cover.
- Made in USA.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
UPC Number	785007013085	Country Of Origin	United States
Material	Brass	Cover Type	Tamper-Resistant
Features	Durable, Hinged Cover	Application Sector	Commercial, Residential
Standard	UL listed	Type	Floor Box cover

Dimensions

Product Width US	6.5 in	Product Height US	0.5 in

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Mounting Type	Box Mounted	Box Cover Position	Horizontal, Vertical
Number of Outlets	1		