



## Open Switches T&B Catalog Number:

**UPC Number:** OT30FT3  
**Status:** 80432541552  
**Description:** Active

3 pole, 30 amps rated at 600 VAC, UL 98, door mounted open non-fusible disconnect switch

### Features

- Quick make, quick brake mechanism
- Extremely compact size
- Finger-proof construction with no hazardous exposed parts

### Application

- Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.
- Motor feeder applications and motor feeder short circuit and ground fault protection

### General

|                 |              |
|-----------------|--------------|
| Style           | Door Mounted |
| Number of Poles | 3            |
| Series          | Non-fusible  |

### Approvals

|          |       |
|----------|-------|
| UL Class | UL 98 |
|----------|-------|

### Dimension Information

|                    |                   |
|--------------------|-------------------|
| H x W x D (inches) | 3.94 x 2.76 x .88 |
|--------------------|-------------------|

### Specifications

|                      |     |
|----------------------|-----|
| Rated Current (Amps) | 30  |
| Rated Voltage AC     | 600 |

### Packaging

|                    |                |
|--------------------|----------------|
| T&B Inner Pack     | 1              |
| Package in Units   | 10             |
| T&B Sold in UOM    | Each           |
| T&B Weight Per UOM | 0.97 lbs. Each |

### For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: techsupport@tnb.com



## Open Switches T&B Catalog Number:

**UPC Number:** OT30FT3  
80432541552  
**Status:** Active  
**Description:**

3 pole, 30 amps rated at 600 VAC, UL 98, door mounted open non-fusible disconnect switch

### Features

Quick make, quick brake mechanism  
Extremely compact size  
Finger-proof construction with no hazardous exposed parts

### Application

Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.  
Motor feeder applications and motor feeder short circuit and ground fault protection

### General

|                 |              |
|-----------------|--------------|
| Style           | Door Mounted |
| Number of Poles | 3            |
| Series          | Non-fusible  |

### Approvals

|          |       |
|----------|-------|
| UL Class | UL 98 |
|----------|-------|

### Dimension Information

|                    |                   |
|--------------------|-------------------|
| H x W x D (inches) | 3.94 x 2.76 x .88 |
|--------------------|-------------------|

### Specifications

|                      |     |
|----------------------|-----|
| Rated Current (Amps) | 30  |
| Rated Voltage AC     | 600 |

### Packaging

|                    |                |
|--------------------|----------------|
| T&B Inner Pack     | 1              |
| Package in Units   | 10             |
| T&B Sold in UOM    | Each           |
| T&B Weight Per UOM | 0.97 lbs. Each |

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com