



**Open Switches**  
**T&B Catalog Number:**

OT100F3  
 80432541587  
 Active

**UPC Number:**  
**Status:**  
**Description:**

3 pole, 100 amps rated at 600 VAC, UL 98, open non-fusible disconnect switch

**Features**

- Quick make, quick brake mechanism
- Extremely compact size
- Finger-proof construction with no hazardous exposed parts

**Application**

Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.  
 Motor feeder applications and motor feeder short circuit and ground fault protection

**General**

Number of Poles 3  
 Series Non-fusible

**Approvals**

UL Class UL 98

**Dimension Information**

H x W x D (inches) 3.94 x 2.76 x 2.93

**Specifications**

Rated Current (Amps) 100  
 Rated Voltage AC 600

**Packaging**

T&B Inner Pack 1  
 Package in Units 10  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 2.07 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com



**Open Switches**  
**T&B Catalog Number:**

OT100F3  
 80432541587  
 Active

**UPC Number:**  
**Status:**  
**Description:**

3 pole, 100 amps rated at 600 VAC, UL 98, open non-fusible disconnect switch

**Features**

- Quick make, quick brake mechanism
- Extremely compact size
- Finger-proof construction with no hazardous exposed parts

**Application**

Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.  
 Motor feeder applications and motor feeder short circuit and ground fault protection

**General**

Number of Poles 3  
 Series Non-fusible

**Approvals**

UL Class UL 98

**Dimension Information**

H x W x D (inches) 3.94 x 2.76 x 2.93

**Specifications**

Rated Current (Amps) 100  
 Rated Voltage AC 600

**Packaging**

T&B Inner Pack 1  
 Package in Units 10  
 T&B Sold in UOM Each  
 T&B Weight Per UOM 2.07 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com