



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



OTM1 250V 1A 1 1/2X13/32 Mid Fuse

Mersen Fuses

Catalog Number	OTM1
Manufacturer	Mersen Fuses
Description	Fuse Otm - Midget - Fast-Acting 250VAC 1A Ferrule Amp-Trap®
Weight per unit	0.0120 (lbs/each)
Product Category	Small Dimension Fuses

Features

AC Voltage Rating	250
amperage rating	1
class	Midget
connection	Ferrule
Fuse Class	Midget
interrupt rating	10
Voltage Rating	250

Material, Color, and Finish

Body Material	Paper
---------------	-------

Dimensions and Weight

Size	1.5 x 0.41
------	------------

Descriptions

Description	250V 1A 1 1/2X13/32 MID FUSE
extra long description	Mersen OTM1 Fuse OTM - Midget - Fas
Features	One-Time OTM midget fuses provide low-cost protection for 250VAC general purpose lighting, heating, control circuits, etc. where time-delay is not required. (Not for Branch Circuit Protection).
Long Description	Fuse OTM - Midget - Fast-Acting 250VAC 1A Ferrule Amp-Trap®
Product Type	Sicherungseinsatz Otm – Miniatur – Flink 250VAC 1A Kapselsic
Short Description	250V 1A 1 1/2x13/32 MID FUSE
Special Features	Low cost and fully rated for economy without compromise Can be used with UltraSafe™ fuse holders 1 1/2" x 13/32" (10 mm x 38 mm) dimensions

Manufacturer Information

Brand	Mersen
GTIN	00782001705015
Manufacturers Part Number	OTM1
UPC	782001705015



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description.....MIDGET FUSES

Type.....Midget Fuses

Packaging

Carton.....1

Package.....10

Weight Per each.....0.012

Uses, Certifications, and Standards

Application.....Supplemental protection of circuits up to 250VAC and 10kA

Mounting.....Clip

standard.....UL Listed to standard 248-14, File E33925 CSA Certified to
Standard C22.2 No. 248.14