



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



12100A6513 Comet, Thru-Beam Detector Wideangle, 20-264 Vac/DC W Eaton Corp

Catalog Number	12100A6513
Manufacturer	Eaton Corp
Description	Eaton Comet 18MM Tubular Photoelectric Sensor, Through Beam, 20 FT Range, Forward Viewing, Output On, 6.6 FT, 300 Ma Ac/DC At 20-264 Vac/15-30 VDC, PVC, Ac: L1 Switched, DC: NPN Open Collector, 20-264 Vac 50/60 HZ, 15-30 VDC (NPN)
Weight per unit	0.6700 (lbs/each)
Product Category	Sensor Accessories

Features

dimensions	2.2000 IN X 0.4700 IN X 0.7100 IN
------------	-----------------------------------

Dimensions and Weight

Height	0.71
Length	2.2
Width	0.47

Descriptions

Description	COMET,THRU-BEAM DETECTOR WIDEANGLE,20-264 VAC/DC W
extra long description	ETN 12100A6513 PHOTO SENSOR,TB DET,
Features	Eaton's Comet Series Photoelectric Sensors is a complete line of high performance, 18 mm tubular sensors with a variety of models and modes to solve virtually any sensing problem.
Long Description	Eaton Comet 18mm tubular photoelectric sensor,Through Beam, 20 ft range, Forward Viewing, Output ON, 6.6 ft, 300 mA AC/DC at 20-264 Vac/15-30 Vdc, PVC, AC: L1 switched, DC: NPN open collector, 20-264 Vac 50/60 Hz, 15-30 Vdc (NPN)
Product Type	Photo Sensor, TB Det, Wide Angle, Acdc, CBL

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113821931
Manufacturers Part Number	12100A6513
UPC	782113821931

Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

Packaging

Carton	1
Weight Per each	0.67



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Vehicles: On-Road - PickUp & Delivery: Food
Operating Temperature	-4° to 158°F (-20° to 70°C)
standard	cUL Recognized,UL Recognized