



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **12NM3106 10/3 6' A/C Whip 1/2"** *Southwire Company*

|                  |  |
|------------------|--|
| Catalog Number   | 12NM3106   |
| Manufacturer     | Southwire Company  |
| Description      | 10-3C BK RD GN Non-Metallic Fixture Whips, 1/2"X6'<br>Non-Metallic Liquidtight Conduit - Type LFNC-B , 10 Per Carton,<br>UL Listed |
| Weight per unit  | 2.1 (lbs/each)   |
| Product Category | Liquid Tight Fittings  |

### **Features**

|                      |   |
|----------------------|---|
| Conductor Size       | 10  |
| connection           | (1) Straight non-metallic liquidtight connector and (1) 90° angle<br>non-metallic connector |
| gauge                | 10 AWG  |
| Inside Diameter      | 0.622/0.642   |
| Material             | PVC   |
| Number of Conductors | 4   |
| outside diameter     | 0.82/0.84   |
| Voltage Rating       | 600V  |

### **Material, Color, and Finish**

|                    |          |
|--------------------|----------|
| Color              | Plain    |
| Conductor Material | Copper   |
| Finish             | Gray PVC |

### **Dimensions and Weight**

|        |     |
|--------|-----|
| Length | 120 |
|--------|-----|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Also Known As...       | Liquid Tight Conduit   |
|                        | Carflex®   |
| extra long description | AFC 8015 10-3c NMTWH 10PCS/CT  |
| Features               | Non-metallic whips are a valuable option for work requiring short cable lengths. Whips are pre-cut lengths of non-metallic conduit, 4 or 6ft long, that are pre-wired, supplied with 12-inch leads for termination, and provided with the appropriate connector on each end, reducing time on the job site. They are great for running power to air conditioning hookups, outdoor lighting, and other outdoor applications such as a disconnect for Jacuzzi or pool filter motors. |
| Long Description       | 10-3c BK RD GN Non-metallic Fixture Whips, 1/2"x6' Non-metallic Liquidtight Conduit - Type LFNC-B , 10 per Carton, UL LISTED   |
| Product Type           | 10-3C NMTWH 10PCS/CT   |
| Short Description      | 10-3c NMTWH 10PCS/CT   |
| similar brands         | Sealtite®  |

## Manufacturer Information

|                           |                  |
|---------------------------|------------------|
| Brand                     | Flexible Conduit |
| GTIN                      | 00077680137302   |
| Manufacturers Part Number | 8015             |
| UPC                       | 077680137302     |

## Taxonomies, Classifications, and Categories

|                      |                                    |
|----------------------|------------------------------------|
| Category Description | NON-METALLIC SEALTITE AND FITTINGS |
| Type                 | Type LFNC-B                        |

## Trade Size

|            |          |
|------------|----------|
| Trade Size | 10-3 STR |
|------------|----------|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 10   |
| Weight Per each | 2.11 |

## Uses, Certifications, and Standards

|                    |                             |
|--------------------|-----------------------------|
| standard           | NEC®410, 430, 440, 250, 356 |
| Temperature Rating | 176                         |