



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1414N4SSI 10X8X4 N4X Lo CLMP CVR

Hammond MFG.

Catalog Number	1414N4SSI
Manufacturer	Hammond MFG.
Description	N4X J Box, Lift Off Cover W/Panel - 10 X 8 X 4 - 304 SS
Weight per unit	11.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

Material	Stainless Steel
----------	-----------------

Material, Color, and Finish

Color	Unpainted
-------	-----------

Dimensions and Weight

Size	10 in x 8 in x 4 in
------	---------------------

Descriptions

Description	10X8X4 N4X LO CLMP CVR
extra long description	HMND 1414N4SSI 10X8X4 CLAMP COVER 3
Long Description	N4X J Box, Lift Off Cover w/panel - 10 x 8 x 4 - 304 SS
Product Type	10X8X4 Clamp Cover 304SS Jic
Special Features	Formed from 14 gauge 304 stainless steel. Smooth, continuously welded seams. Welded brackets provide for enclosure mounting. Lift-Off cover is secured with stainless steel clamps and screws. Seamless poured-in place gasket. All models larger than 4" x 4" include a removable 14 gauge inner panel. Tapped studs are provided for mounting inner panels. A bonding stud is provided on the door and a grounding stud is provided in the enclosure.

Manufacturer Information

Brand	Hammond MFG.
GTIN	00623980295251
Manufacturers Part Number	1414N4SSI
UPC	623980295251

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	N4X J Box, Lift Off Cover w/panel

Packaging

Carton	1
Weight Per each	11



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes or terminal wiring enclosures. Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion may be a problem.

Mounting

WALL

nema rating

type-3r, type-13, type-4x

standard

CSA, UL, CE