



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



161284XS Encl 16X12X8 N4X 1DR CH *Cooper B-Line/Cable Tray*

Catalog Number	161284XS
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 16" Height, 8" Length, 16" Width, Nema 4X, Hinged Cover, 4XS Enclosure, Wall Mount, Small Single Door, External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	21.8 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

dimensions	8.0000 IN X 16.0000 IN X 16.0000 IN
Material	304 Stainless Steel
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	12.00 In Width X 8.00 In Depth X 16.00 In Height
------	--

Descriptions

Description	ENCL 16X12X8 N4X 1DR CH
extra long description	B-LINE 16128-4XS TYPE 4X SSL SGL-DO
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure, 16" height, 8" length, 16" width, NEMA 4X, Hinged cover, 4XS enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket
Product Type	Type 4X SSL SGL-Door Enc, 16X12X8
Special Features	Stainless door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051406863
Manufacturers Part Number	16128-4XS
UPC	782051406863

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Wall mounted panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	21.8

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Datacenters - IT Space: CI and Hyper Converged Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - Aftermarket Other IT and Datacom - IT and Datacomm - Other Utility - Substations, Utility Transmission and Distribution Commercial / Institutional Buildings / Structures - Power Distribution and Controls Commercial / Institutional Buildings / Structure
Mounting	EXTERNAL FEET, WALL
nema rating	4X
standard	CSA C22.2, UL 50, NEMA