




Commercial grade straight blade receptacles

Product description


2-pole, 3-wire grounding
 15A, 125V/AC
 20A, 125V/AC
 NEMA 5-15R, 5-20R




BR20



CR20



1877



6352

Commercial grade receptacles



| Rating | | NEMA | Description | Color suffix | Catalog no. | |
|--------|------|-------|-------------------------------------|----------------------------|-------------|-------|
| A | V/AC | | | | | |
| 15 | 125 | 5-15R | Duplex receptacle, back & side wire | A, B, BK, GY, LA, V, W | □ BR15__ | • • • |
| | | | Duplex receptacle, side wire | A, B, BK, GY, LA, V, W | □ CR15__ | • • • |
| | | | Single receptacle, side wire | B, BK, LA, V, W | □ 817__* | • • • |
| 20 | 125 | 5-20R | Duplex receptacle, back & side wire | A, B, BK, GY, LA, RD, V, W | □ BR20__ | • • • |
| | | | Duplex receptacle, side wire | A, B, BK, GY, LA, V, W | □ CR20__ | • • • |
| | | | Single receptacle, side wire | A, B, BK, LA, V, W | □ 1877__* | • • • |

* Not Fed Spec

Decorator commercial grade receptacles



| Rating | | NEMA | Description | Color suffix | Catalog no. | |
|--------|------|-------|-------------------------------------|------------------------|-------------|-------|
| A | V/AC | | | | | |
| 15 | 125 | 5-15R | Duplex receptacle, back & side wire | B, BK, GY, LA, V, W | □ 6252__† | • • • |
| | | | Single receptacle, back & side wire | V, W | □ 6250__* | • • • |
| 20 | 125 | 5-20R | Duplex receptacle, back & side wire | A, B, BK, GY, LA, V, W | □ 6352__† | • • • |
| | | | Single receptacle, back & side wire | B, V, W | □ 6350__*† | • • • |

† Not NOM cert, * UL Listed & CSA certified

Accessories for construction grade 5-15 & 5-20 receptacles

| Description | Color suffix | Catalog no. | |
|--|----------------------------|-------------|-----|
| 2-Gang standard size duplex receptacle wallplate | A, B, BK, GY, LA, RD, V, W | □ 5150__ | • • |
| 1-Gang mid-size single receptacle wallplate, 1.4" hole | A, B, BK, GY, LA, RD, V, W | □ PJ7__ | • |



5150B



PJ7GY

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)



Specification information: Commercial receptacles: A-33

Compliances, specifications and availability are subject to change without notice.

Build-to-spec customizable devices - Page A-6

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32