



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2038EINS Long Nose Side Cutter Pliers, 8-In Slim Insulated

Klein Tools

| | |
|------------------|---|
| Catalog Number | 2038EINS |
| Manufacturer | Klein Tools |
| Description | Long Nose Side Cutter Pliers, 8-In Slim Insulated |
| Weight per unit | 0.7000 (lbs/each) |
| Product Category | Pliers, Wrenches, Saw, Pouches |

Features

| | |
|----------------|--------------------------|
| Handle Length | 4.67" (11.9 cm) |
| Jaw Length | 2.32" (5.9 cm) |
| jaw thickness | 0.5" (1.3 cm) |
| Jaw Width | 1.02" (2.6 cm) |
| knife length | 0.693" (1.8 cm) |
| Material | Induction Hardened Steel |
| media | Yes |
| Point Diameter | 0.125" (0.32 cm) |

Material, Color, and Finish

| | |
|--------------|-------------|
| Handle Color | Orange/Gray |
|--------------|-------------|

Dimensions and Weight

| | |
|----------------|-----------------|
| Overall Length | 8.77" (22.3 cm) |
|----------------|-----------------|

Descriptions

| | |
|------------------------|---|
| Description | LONG NOSE SIDE CUTTER PLIERS, 8-IN SLIM INSULATED |
| extra long description | KLEIN 2038EINS Long Nose Pliers Sli |
| Long Description | Long Nose Side Cutter Pliers, 8-In Slim Insulated |
| Product Type | Long Nose Pliers Slim Side Cut, Ins |
| Special Features | Flame Retardant and Impact Resistant Handle |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Klein Tools |
| GTIN | 00092644710476 |
| Manufacturers Part Number | 2038EINS |
| UPC | 092644710476 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | HAND TOOLS |
| Type | Long Nose Side Cutting Pliers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-----------------|
| Carton | 1 |
| Package | 3 |
| Weight | 11.2 oz (318 g) |
| Weight Per each | 0.7 |

Uses, Certifications, and Standards

| | |
|-------------|---------------------------------|
| Application | For Work Near Energized Sources |
| standard | IEC 60900 and ASTM F1506 |