



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 24308SD Encl 24X30X8 N4 1DR QT CH *Cooper B-Line/Cable Tray*

Catalog Number	24308SD
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 24" Height, 8" Length, 30" Width, Nema 4, Hinged Cover, SD Enclosure, Wall Mount, Medium Single Door, Thru Holes, Optional External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	59.3 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

### Features

dimensions	8.0000 IN X 30.0000 IN X 24.0000 IN
Mounting Type	Wall

### Material, Color, and Finish

Color	Gray
-------	------

### Dimensions and Weight

Size	30.00 In Width X 8.00 In Depth X 24.00 In Height
------	--

### Descriptions

Description	ENCL 24X30X8 N4 1DR QT CH
extra long description	B-LINE 24308-SD TYPE 4/12 SGL SOLID
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure,24" height,8" length,30" width,NEMA 4,Hinged cover,SD enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket
Product Type	Type 4/12 SGL Solid Door Enc, 24X30X8
Special Features	1/4 turn latches

### Manufacturer Information

Brand	Eaton
GTIN	00782051091946
Manufacturers Part Number	24308-SD
UPC	782051091946

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Wall mounted panel enclosure



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	59.341

## Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative Energy Datacenters - IT Space: CI and Hyper Converged Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other Commercial / Institutional Buildings / Structures - Critical Power Other IT and Datacom - IT and Datacomm - Other Utility - Substations, Utility Transmission and Distribution Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - Aftermarket Commercial / Institutional Buildings /
Mounting standard	WALL CSA C22.2, UL 50, NEMA