



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



240722 M12 3/8 Drill/Driver Kit *Milwaukee Electric Tool*

| | |
|------------------|--|
| Catalog Number | 240722 |
| Manufacturer | Milwaukee Electric Tool |
| Description | Drill and Fasten Up to 35% Faster With The Only Tool In Its Class That Has An All-Metal Locking Chuck. The Powerful M12™ Cordless Lithium-Ion 3/8 In. Drill/Driver Delivers 275 In-LBS Of Torque – Up to 25% More Torque Than The Competition – and 0-400/0 to 1, 500 RPM. Its Compact, Lightweight and Durable Design Means Greater Comfort and Efficiency On The Jobsite. The All-Metal Single-Sleeve Ratcheting Chuck Offers Superior Bit Grip, So You Won'T Have to Stop For Bit Re Tightening or Lost Bits. The Inboard Led |
| Weight per unit | 5.2 (lbs/each) |
| Product Category | Battery Driven Tools |

Features

| | |
|-----------------|---------|
| Battery Voltage | 12 |
| media | Yes |
| Switch Type | Trigger |

Material, Color, and Finish

| | |
|------------------|--------------------|
| Housing Material | Glass-filled Nylon |
|------------------|--------------------|

Dimensions and Weight

| | |
|--------|------|
| Length | 6.94 |
| Width | 2.22 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | M12 3/8 DRILL/DRIVER KIT |
| extra long description | MILW 2407-22 M12 3/8" Drill/Driver |
| Features | The M12 series offers solutions that deliver portable productivity. They take on the tightest spaces and are specifically built to go anywhere. They are trade focused, system wide, lightweight with ergonomic design make portability easy, and operation faster and more productive. |
| Long Description | Drill and fasten up to 35% faster with the only tool in its class that has an all-metal locking chuck. The powerful M12™ cordless lithium-ion 3/8 in. drill/driver delivers 275 in-lbs of torque – up to 25% more torque than the competition – and 0-400/0 to 1,500 RPM. Its compact, lightweight and durable design means greater comfort and efficiency on the jobsite. The all-metal single-sleeve ratcheting chuck offers superior bit grip, so you won't have to stop for bit re tightening or lost bits. The inboard LED |
| Product Type | M12 3/8" Drill/Driver Kit |
| Short Description | M12 3/8 Drill/Drv'r Kt |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242300785 |
| Manufacturers Part Number | 2407-22 |
| UPC | 045242300785 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------|
| Category Description | POWER TOOLS |
|----------------------|-------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 5.24 |