



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2621 SW Dec 1P 20A 120/277V Grounded BR

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 2621 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Single-Pole, Back and Side-Wire, Decorator Switch, 20A, 120/277V. |
| Weight per unit | 0.1970 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-------------------|
| amperage rating | 20 |
| Contact Rating | 20Amp, 120/277Vac |
| insulation | Bare |
| media | Yes |
| Poles | spst |
| Switch Type | Paddle |
| Voltage | 120/277 V |
| Voltage Rating | 120/277 |
| Wattage | 1 |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Color | Brown |
| Finish | Matte |

Dimensions and Weight

| | |
|------|-------|
| Size | 4.25" |
|------|-------|

Descriptions

| | |
|------------------------|---|
| Description | SW DEC 1P 20A 120/277V GROUNDED BR |
| extra long description | P&S 2621 SW DEC 1P 20A 120/277V GRO |
| Features | Decorator Style |
| Long Description | Single-Pole, Back and Side-Wire, Decorator Switch, 20A, 120/277V. |
| Product Type | SW Dec 1P 20A 120/277V Grounded BN |
| Special Features | Impact resistant polycarb back body & frame, cushioned thermoplastic paddle , unique single rocking butterfly contact |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007539301 |
| Manufacturers Part Number | 2621 |
| UPC | 785007539301 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.197 |

Uses, Certifications, and Standards

| | |
|-------------|-----------------------|
| Application | Industrial |
| Enclosure | Wall box |
| Mounting | WALL |
| standard | CSA, UL, CULUS, UL 20 |