



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



266RT 2-1/2" Diecast Emt Raintight Compression Coupling

Bridgeport Fittings

| | |
|------------------|---------------------------|
| Catalog Number | 266RT |
| Manufacturer | Bridgeport Fittings |
| Description | 2-1/2" Raintight Coupling |
| Weight per unit | 1.5 (lbs/each) |
| Product Category | Liquid Tight Fittings |

Features

| | |
|------------------|-------------|
| Connector Type | Compression |
| media | Yes |
| outside diameter | 3.44 |

Dimensions and Weight

| | |
|--------|------|
| Length | 3.75 |
|--------|------|

Descriptions

| | |
|------------------------|---|
| Description | 2-1/2" DIECAST EMT RAIN TIGHT COMPRESSION COUPLING |
| extra long description | BPT 266-RT 2-1/2" RAIN TIGHT CPLG |
| Features | Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations. |
| Long Description | 2-1/2" Raintight Coupling |
| Product Type | 2-1/2" Rain Tight CPLG |
| Special Features | With Bridgeport's newly redesigned Raintight Compression Couplings, 266-RT through 269-RT, contractors can install just one wet location fitting for either thread less Rigid / IMC or EMT. |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Bridgeport Fittings |
| GTIN | 00781747142665 |
| Manufacturers Part Number | 266RT |
| UPC | 781747142665 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | DIECAST EMT FITTINGS |
| Type | Raintight |

Trade Size

| | |
|------------|-----|
| Trade Size | 2.5 |
|------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 12 |
| Weight Per each | 1.525 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

These 2-1/2" dual Listed Zinc Alloy fittings come standard with a 105° C temperature rated insulated throat and the words "Rigid / EMT and RAINIGHT" clearly cast into the body. This marking helps the AHJ to precisely confirm the products intended use.

Patented

standard

cULus