



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



26W47 Turnlok Plug IP67 20A 125V L520P

Pass & Seymour/LeGrand

| | |
|------------------|---|
| Catalog Number | 26W47 |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Locking Watertight Plug, 20AMP 125VOLT, Nema Configuration L5-20, Multipoint Sealing System Provides Environmental Protection Of: Nema 4, 4X, 6, 6P and IP67 Rated. |
| Weight per unit | 0.5800 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|---|
| amperage rating | 20 |
| Cord Type | 12/3 SJ, 14/3 S to 10/3 S, .475" min to .720" max |
| Material | Rubber |
| Number of Wires | 3 |
| Phase | 1 |
| Poles | 2 |
| Voltage Rating | 125 |
| Wire Size | 14-10 |

Descriptions

| | |
|------------------------|--|
| Description | TURNLOK PLUG IP67 20A 125V L520P |
| extra long description | P&S 26W47 TURNLOK PLUG IP67 20A 125 |
| Long Description | Locking Watertight Plug, 20amp 125volt, NEMA Configuration L5-20, multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P and IP67 rated. |
| Product Type | Turnlok Plug IP67 20A 125V L520P |
| Special Features | Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007032611 |
| Manufacturers Part Number | 26W47 |
| UPC | 785007032611 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type | LOCKING PLUG |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.58 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings Ideal for washdown areas — rated wa |
| environmental conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized |
| nema rating | L5-20P |
| standard | UL Listed, CSA Listed |