



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



254RTI2 1-1/2" Raintight Diecast Compression Connector *Bridgeport Fittings*

| | |
|------------------|---|
| Catalog Number | 254RTI2 |
| Manufacturer | Bridgeport Fittings |
| Description | 1-1/2" Raintight Compression Connector, Insulated |
| Weight per unit | 0.5450 (lbs/each) |
| Product Category | Die Cast Insulated Straight CO |

Features

| | |
|----------------|------------------|
| Connector Type | Compression |
| insulation | Insulated Throat |
| media | Yes |

Material, Color, and Finish

| | |
|--------|--------------|
| Finish | Ball burnish |
|--------|--------------|

Dimensions and Weight

| | |
|------|-------|
| Size | 1-1/2 |
|------|-------|

Descriptions

| | |
|------------------------|--|
| Description | 1-1/2" RAIN TIGHT DIECAST COMPRESSION CONNECTOR |
| extra long description | BPT 254-RTI2 1-1/2" INS RAIN TIGHT |
| Features | Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations. |
| Long Description | 1-1/2" Raintight Compression Connector, Insulated |
| Product Type | 1-1/2" Ins Rain Tight Compress |
| Special Features | Raintight |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Bridgeport |
| GTIN | 00781747192547 |
| Manufacturers Part Number | 254-RTI2 |
| UPC | 781747192547 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------|
| Category Description | METALLIC FITTINGS |
| Type | CONNECTOR |

Trade Size

| | |
|------------|-------|
| Trade Size | 1-1/2 |
|------------|-------|

Packaging

| | |
|-----------------|-------|
| Carton | 10 |
| Package | 40 |
| Weight Per each | 0.545 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting EMT to box or enclosure. Insulated Throat - 90° C. Patented

standard

UL