



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 256RTI2 2-1/2" Raintight Diecast Compression Connector

*Bridgeport Fittings*

|                  |  |
|------------------|--|
| Catalog Number   | 256RTI2  |
| Manufacturer     | Bridgeport Fittings                              |
| Description      | 2-1/2" Raintight Insulated Connector, NPT Thread |
| Weight per unit  | 1.2 (lbs/each)                                   |
| Product Category | Liquid Tight Fittings                            |

### Features

|                |                  |
|----------------|------------------|
| Connector Type | Compression      |
| insulation     | Insulated Throat |
| media          | Yes              |

### Dimensions and Weight

|      |       |
|------|-------|
| Size | 2-1/2 |
|------|-------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 2-1/2" RAIN TIGHT DIECAST COMPRESSION CONNECTOR                        |
| extra long description | BPT 256-RTI2 2-1/2" RAIN TIGHT INS                                     |
| Features               | Think Orange: Quality In, Water Out. Listed for Damp or Wet Locations. |
| Long Description       | 2-1/2" Raintight Insulated Connector, NPT THREAD                       |
| Product Type           | 2-1/2" Rain Tight Ins Conn   |
| Special Features       | The Dual Internal sealing rings create a raintight seal.               |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Bridgeport     |
| GTIN                      | 00781747192561 |
| Manufacturers Part Number | 256-RTI2       |
| UPC                       | 781747192561   |

### Taxonomies, Classifications, and Categories

|                      |                       |
|----------------------|-----------------------|
| Category Description | METALLIC FITTINGS     |
| Type                 | Raintight Compression |

### Trade Size

|            |       |
|------------|-------|
| Trade Size | 2-1/2 |
|------------|-------|

### Packaging

|                 |        |
|-----------------|--------|
| Carton          | 12     |
| Weight Per each | 1.1916 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Compression style connector with internal sealing ring and knockout gasket to create a raintight seal when connecting EMT to box or enclosure. With Bridgeport's newly redesigned Raintight Compression Connectors, 256-RTI2 thru 259-RTI2, contractors can install just one wet location fitting for either thread less Rigid / IMC or EMT. These 2-1/2" dual Listed Zinc Alloy fittings come standard with a 105° C temperature rated insulated throat and the words "Rigid / EMT and RAIN TIGHT" clearly cast into the body.

standard

cULus