

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460095](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)      [Product Literature \(PDF\)](#)

**Agency Certification**

CSA                      LR6837  
 UL                      E10176

**General**

Product Family                      Wiring Devices  
 Series                      [130146](#)  
 IP Rating                      IP67  
 NEMA Configuration                      NEMA L7-15  
 Overview                      [Watertite® Wet-Location Wiring Solutions](#)  
 Product Literature Order No                      987650-8067  
 Product Name                      Watertite  
 Receptacle Type                      Single  
 Specialty                      N/A  
 Type                      Connector  
 UPC                      78678871304  
 Woodhead                      Yes

**Physical**

Cord Grip Body Size                      F2 1/2"  
 Flange                      No  
 Flip Lid                      No  
 Gender                      Female  
 Length                      N/A  
 Locking Blade                      Yes  
 Poles                      2-pole/3-wire

**Electrical**

Cord Type                      N/A  
 Current - Maximum per Contact                      15.0A  
 GFCI                      No  
 Lighted Connector                      No  
 Voltage - Maximum                      277V

**Material Info**

Engineering Number                      25W34



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS                      Not Reviewed

ELV                      Not Relevant

RoHS Phthalates                      Not Reviewed

**Search Parts in this Series**

[130146 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460095](#)  
**Status:** **Active**  
**Overview:** [Watertite® Wet-Location Wiring Solutions](#)  
**Description:** Watertite Connector with Locking Blade, 2 Pole/3 Wire, NEMA L7-15, 277V, Cord Grip Body Size F2

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR6837  
UL E10176

**General**

Product Family Wiring Devices  
Series [130146](#)  
IP Rating IP67  
NEMA Configuration NEMA L7-15  
Overview [Watertite® Wet-Location Wiring Solutions](#)  
Product Literature Order No 987650-8067  
Product Name Watertite  
Receptacle Type Single  
Specialty N/A  
Type Connector  
UPC 78678871304  
Woodhead Yes

**Physical**

Cord Grip Body Size F2 1/2"  
Flange No  
Flip Lid No  
Gender Female  
Length N/A  
Locking Blade Yes  
Poles 2-pole/3-wire

**Electrical**

Cord Type N/A  
Current - Maximum per Contact 15.0A  
GFCI No  
Lighted Connector No  
Voltage - Maximum 277V

**Material Info**

Engineering Number 25W34



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Not Reviewed  
ELV Not Relevant  
RoHS Phthalates Not Reviewed

**Search Parts in this Series**

[130146 Series](#)