





CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET					★	Ⓢ		
					NJ	IL	TX	CA	GA				
GR8 Series													
	2'x2'												
	2GR8-2U6T8A-UNV-EB81-U	2 LAMP, 2'X2' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 U6	623961643842	12.2	1	56	•	•	•	•	•	★	Ⓢ
	GR82U	2 U-LAMP, 2'X2' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	623961182563	15.13	1	48						★	Ⓢ
	APT-2U6T8	2 LAMP, 2'X2' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM U6T8 UNV ELECTRONIC BALLAST	080083621958	12.2	1	56	•	•	•	•	•	★	Ⓢ
	2'x4'												
	GR8	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	622697079918	22.5	1	28						★	Ⓢ
	GR83	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	623961285875	22.5	1	24						★	Ⓢ
	GR8-232A-UNV-EB81-U	2 LAMP, 1'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8	662401551330	16.2	1	33	•					★	
	2GR8-232A125-UNV-EB81-U	2 LAMP, 2'X4' SPECIFICATION GRADE LENSED TROFFER W/.125 LENS, CEE LISTED ELECTRONIC BALLAST, T8	623961689376	20.5	1	28						★	
	2GR8-232A-UNV-EB81-U	2 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8	623961759802	22.5	1	28	•	•	•	•	•	★	Ⓢ
	2GR8-232A-UNV-L8735-EB81-U	2 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	662401340095	21.85	1	24			•			★	
	2GR8-332A125-UNV-EB81-U	3 LAMP, 2'X4' SPECIFICATION GRADE LENSED TROFFER W/.125 LENS, CEE LISTED ELECTRONIC BALLAST, T8	623961689697	20.5	1	24						★	
	2GR8-332A-UNV-EB81-U	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8	662401286805	20.5	1	28	•	•	•	•	•		Ⓢ
	2GR8-332A-UNV-EB82-U	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST (2), T8	662401341405	22.5	1	28		•		•	•	★	Ⓢ
	2GR8-332A-UNV-L8735-A3/8-2/18G-EB81-U	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	662401335831	23.83	1	28		•		•	•	★	Ⓢ
	2GR8-332A-UNV-L8735-EB81-U	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	662401012213	21.85	1	28		•	•			★	Ⓢ
	2GR8-332A-UNV-L8741-A3/8-2/18G-EB81-U	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	623961689840	23.83	1	28						★	Ⓢ
	2GR8-432A125-UNV-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, #12 .125 THICK ACRYLIC LENS, CEE LISTED ELECTRONIC BALLAST, T8	662401334247	20.5	1	24						★	
	2GR8-432A-UNV-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8	662401286812	20.5	1	28	•	•	•	•	•	★	Ⓢ
	2GR8-432A-UNV-EB82-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST (2), T8	662400102229	22.5	1	24			•	•	•	★	Ⓢ
	2GR8-432A-UNV-L8735-A3/8-2/18G-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	662401335848	24.28	1	28		•		•	•	★	Ⓢ
2GR8-432A-UNV-L8735-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	662401335862	22.3	1	28			•				Ⓢ	
2GR8-432A-UNV-L8741-A3/8-2/18G-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	662401321902	22.5	1	28	•						Ⓢ	
2GR8-432A-UNV-L8741-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	623961689482	22.3	1	28	•	•					Ⓢ	

★ Indicates ARRA Eligible Product Ⓢ Indicates EISA Compliant Pulse Start Products Ⓢ Indicates Off the Shelf Product

Please reference the Cooper Lighting Stock Guide Terms and Conditions page. Pictures are a representation of product categories and may not illustrate the exact skus listed. Product information is subject to change without notice. Consult factory representative for additional information and inventory details. Visit www.cooperlighting.com for more product information.

CATALOG NUMBER	DESCRIPTION	UPC CODE	WEIGHT	CASE QTY	PALLET					★	Ⓢ			
					QTY	NJ	IL	TX	CA			GA		
GR8 Series														
	2'x2'													
	2GR8-2U6T8A-UNV-EB81-U	2 LAMP, 2'X2' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 U6	623961643842	12.2	1	56	•	•	•	•	•	★	Ⓢ	
	GR82U	2 U-LAMP, 2'X2' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	623961182563	15.13	1	48						•	★	Ⓢ
	APT-2U6T8	2 LAMP, 2'X2' LENSED TROFFER, PRISMATIC LENS, NEMA PREMIUM U6T8 UNV ELECTRONIC BALLAST	080083621958	12.2	1	56	•	•	•	•	•	★	Ⓢ	
	2'x4'													
	GR8	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	622697079918	22.5	1	28						•	★	Ⓢ
	GR83	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	623961285875	22.5	1	24						•	★	Ⓢ
	GR8-232A-UNV-EB81-U	2 LAMP, 1'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8	662401551330	16.2	1	33		•				•	★	
	2GR8-232A125-UNV-EB81-U	2 LAMP, 2'X4' SPECIFICATION GRADE LENSED TROFFER W/.125 LENS, CEE LISTED ELECTRONIC BALLAST, T8	623961689376	20.5	1	28						•	★	
	2GR8-232A-UNV-EB81-U	2 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8	623961759802	22.5	1	28	•	•	•	•	•	•	★	Ⓢ
	2GR8-232A-UNV-L8735-EB81-U	2 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	662401340095	21.85	1	24			•				★	
	2GR8-332A125-UNV-EB81-U	3 LAMP, 2'X4' SPECIFICATION GRADE LENSED TROFFER W/.125 LENS, CEE LISTED ELECTRONIC BALLAST, T8	623961689697	20.5	1	24						•	★	
	2GR8-332A-UNV-EB81-U	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8	662401286805	20.5	1	28	•	•	•	•	•	•	★	Ⓢ
	2GR8-332A-UNV-EB82-U	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST (2), T8	662401341405	22.5	1	28		•				•	★	Ⓢ
	2GR8-332A-UNV-L8735-A3/8-2/18G-EB81-U	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	662401335831	23.83	1	28		•				•	★	Ⓢ
	2GR8-332A-UNV-L8735-EB81-U	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	662401012213	21.85	1	28		•	•			•	★	Ⓢ
	2GR8-332A-UNV-L8741-A3/8-2/18G-EB81-U	3 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	623961689840	23.83	1	28						•	★	Ⓢ
	2GR8-432A125-UNV-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, #12 .125 THICK ACRYLIC LENS, CEE LISTED ELECTRONIC BALLAST, T8	662401334247	20.5	1	24						•	★	
	2GR8-432A-UNV-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8	662401286812	20.5	1	28	•	•	•	•	•	•	★	Ⓢ
	2GR8-432A-UNV-EB82-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST (2), T8	662400102229	22.5	1	24			•	•	•	•	★	Ⓢ
	2GR8-432A-UNV-L8735-A3/8-2/18G-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	662401335848	24.28	1	28		•				•	★	Ⓢ
2GR8-432A-UNV-L8735-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	662401335862	22.3	1	28			•			•	★	Ⓢ	
2GR8-432A-UNV-L8741-A3/8-2/18G-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS & FLEX	662401321902	22.5	1	28	•					•	★	Ⓢ	
2GR8-432A-UNV-L8741-EB81-U	4 LAMP, 2'X4' STATIC LENSED TROFFER, CEE LISTED ELECTRONIC BALLAST, T8 W/LAMPS	623961689482	22.3	1	28	•	•				•	★	Ⓢ	

★ Indicates ARRA Eligible Product Ⓢ Indicates EISA Compliant Pulse Start Products Ⓢ Indicates Off the Shelf Product

Please reference the Cooper Lighting Stock Guide Terms and Conditions page. Pictures are a representation of product categories and may not illustrate the exact skus listed. Product information is subject to change without notice. Consult factory representative for additional information and inventory details. Visit www.cooperlighting.com for more product information.