

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470081](#)
Status: **Active**
Overview: [Watertite Wet-Location Wiring Solutions](#)
Description: Watertite Plug with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V, Cord Grip Body Size F4

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E10176

General

Product Family Wiring Devices
 Series [130147](#)
 Exclude SD Check Yes
 IP Rating IP67
 NEMA Configuration NEMA L16-30
 Overview [Watertite Wet-Location Wiring Solutions](#)
 Product Literature Order No 987650-8067
 Product Name Watertite
 Receptacle Type N/A
 Specialty N/A
 Type Plug
 UPC 78678871234

Physical

Cord Grip Body Size F4 1"
 Flange No
 Flip Lid No
 Gender Male
 Length N/A
 Locking Blade Yes
 Net Weight 290.298/g
 Poles 3-pole/4-wire

Electrical

Cord Type N/A
 Current - Maximum per Contact 30.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 3ø 480V

Material Info

Engineering Number 28W76



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130147 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301470081](#)
Status: **Active**
Overview: Watertite Wet-Location Wiring Solutions
Description: Watertite Plug with Locking Blade, 3 Pole/4 Wire, NEMA L16-30, 3Ø 480V, Cord Grip Body Size F4

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

| | |
|-----|--------|
| CSA | LR6837 |
| UL | E10176 |

General

| | |
|-----------------------------|--|
| Product Family | Wiring Devices |
| Series | 130147 |
| Exclude SD Check | Yes |
| IP Rating | IP67 |
| NEMA Configuration | NEMA L16-30 |
| Overview | <u>Watertite Wet-Location Wiring Solutions</u> |
| Product Literature Order No | 987650-8067 |
| Product Name | Watertite |
| Receptacle Type | N/A |
| Specialty | N/A |
| Type | Plug |
| UPC | 78678871234 |

Physical

| | |
|---------------------|---------------|
| Cord Grip Body Size | F4 1" |
| Flange | No |
| Flip Lid | No |
| Gender | Male |
| Length | N/A |
| Locking Blade | Yes |
| Net Weight | 290.298/g |
| Poles | 3-pole/4-wire |

Electrical

| | |
|-------------------------------|---------|
| Cord Type | N/A |
| Current - Maximum per Contact | 30.0A |
| GFCI | No |
| Lighted Connector | No |
| Voltage - Maximum | 3Ø 480V |

Material Info

| | |
|--------------------|-------|
| Engineering Number | 28W76 |
|--------------------|-------|



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130147](#) Series