



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



306162 Weatherproof Wire Conn, 61/62, 5 Each, 10/Card

Ideal

| | |
|------------------|--------------------------------|
| Catalog Number | 306162 |
| Manufacturer | Ideal |
| Description | 61 62 Weathprf Asrtd 10 Clam |
| Weight per unit | 0.0100 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|----------|------------|
| Quantity | Card of 10 |
|----------|------------|

Material, Color, and Finish

| | |
|-------|-------------|
| Color | Gray-Orange |
|-------|-------------|

Descriptions

| | |
|------------------------|---|
| Description | WEATHERPROOF WIRE CONN, 61/62, 5 EACH, 10/CARD |
| extra long description | IDEAL 30-6162 61 62 WEATHRPRF ASRTD |
| Features | 100% Silicone-based sealant protects against moisture and corrosionUL Listed to 486G Sealed Twist-On Wire Connector for use in damp/wet locations or above-grade applicationsEasy to apply, pre-filled twist-on wire connectorsSwept wing design is built for comfort and efficiencyEliminates the need for heat-shrink or excessive tapingTough, UL 94V-2 flame-retardant shell rated at 105°C (221°F)Models 61 and 63 approved for bonding and grounding applicationsFor use in damp/wet location or above-grade applications |
| Long Description | 61 62 WEATHRPRF ASRTD 10 CLAM |
| Product Type | 61 62 Weathprf Asrtd 10 Clam |
| Special Features | Hexagonal shape allows connectors to be applied with standard nutdriver. Silicone-based sealant protects against moisture and corrosion. Easy to apply pre-filled twist-on wire connectors |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250758135 |
| Manufacturers Part Number | 30-6162 |
| UPC | 783250758135 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------------|
| Category Description | WIRE NUTS |
| Type | Model 61® & Model 62® Combo Pack |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.01 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Model 61® Handles wire sizes from #22 to #14 AWG copper.
Model 61® Minimum of 2 #20 AWG. Model 61® Maximum of 2
#14 AWG. Model 62® Handles wire sizes from #18 to #8 AWG
copper. Model 62® Minimum of 2 #18 AWG. Model 62®
Maximum of 3 #10 AWG.

standard

UL listed for 486D for use in damp/wet locations